


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



SCHOTT NG Gray Glass Neutral Density (ND) Filters



Stock #14-106 ■ In Stock



1



€93,00

ADD TO CART

Qty 1-10

€93,00

Qty 11+

€82,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Optical Density OD (Average):
0.25

Glass/Filter Number: <a>SCHOTT NG11
Length (mm): 50.00
Coating: Uncoated
Index of Refraction n_d: 1.52
Surface Quality: 60-40
Transformation Temperature (°C): 481
Thickness (mm): 2.00 ±0.2
Transmission (%): 56
Transmission Tolerance (%): (nominal)
Type: Neutral Density Filter
Width (mm): 50.00
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Optical Density Tolerance (%): (nominal)

Regulatory Compliance

RoHS: <a>Compliant
Certificate of Conformance: <a>View