

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

ST Main Body with Iris, T-Mount, KC VideoMax



#86-890: ST Main Body with Iris, T-Mount, KC VideoMax



Stock #86-890 3-4 DAYS



1



€3.025,00

ADD TO CART

Qty 1+

€3.025,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:

0.10X - 0.21X: 64 - 30mm
0.2X - 0.5X: 32 - 12.8mm

Weight (lbs):

0.54

Note:

0.2X - 0.5X w/ Auxiliary Lens, Working Distance: 940 - 405mm

Type: Long Distance Microscope
Primary Magnification PMAG: 0.10X - 0.21X
Maximum Sensor Format: 35mm
Working Distance (mm): 965 - 1,880
Mount: M42 x 0.75 (T-Mount)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View