

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #12-741 3-4 DAYS



1



€280,00

ADD TO CART

Qty 1-5

€280,00

Qty 6+

€252,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
Gray

Optical Density OD (Average):
>5 @ 190 - 400nm
>5 @ 1025 - 1075nm
>6 @ 1035 - 1070nm

>7 @ 1045 - 1065nm

Visible Light Transmission VLT (%):
55

EN 207/208 Ratings:
DIR LB5 + MLB5Y @ 1,025-1,075nm, DIR LB6 + M
LB6Y @ 1,035-1,070nm, D LB6, IR LB7 + MLB7YS @
1,045-1,065nm

Filter Material:
Polymer

Filter:
LS12

Style:
Adjustable Temples Wrap Around

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)
