

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #15-829 3-4 DAYS



1



€290,00

ADD TO CART

Qty 1-5

€290,00

Qty 6+

€261,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Thickness (inches):
0.009

Thickness (mm):
0.24

Note:
Recommended Pulsed Width: 1ns to 30ms
Recommended Power Level Range: 5 mJ/cm² to 20 J/cm²

Sheet Size (in):
20 x 24

Sheet Size (mm):
580 x 609.6

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)