

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

Zero Aperture, 12mm Max. Aperture, Iris Diaphragm



Stock #53-906 In Stock

-

1

+

 €50,00

ADD TO CART

Qty 1-9

€50,00

Qty 10+

€44,20

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):

12.0
Outer Diameter (mm): 21.0
Construction: Black Anodized Aluminum, Black Spring Steel Leaves, Stainless Steel Pins
Lever Diameter (mm): 3.00
Lever Length (mm): 11.80
Number of Leaves: Two Sets of 5
Spacing of Leaf Layers (mm): 2.5
Thickness (mm): 6.20

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)