



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



SURFACE: IMA
DIA: 0.000 MM

SPOT DIAGRAM



45174
TUE DEC 16 2008 UNITS ARE μm .
FIELD : 1
RMS RADIUS : 61.075
GD RADIUS : 157.989
SCALE BAR : 400

REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

45174
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 119.5972 μm
DIFFRACTION LIMITED RANGE: 6.823 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT

45174
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 500.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

45174
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm .
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



www.edmundoptics.com