



# TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy



TECHSPEC® ACHROMATIC LENSES



SURFACE: INA  
DIA: 0.000 MM  
SPOT DIAGRAM  
47636INK  
TUE DEC 16 2008 UNITS ARE μm.  
FIELD : :  
RMS RADIUS : 91.111  
GD RADIUS : 218.255  
SCALE BAR : 1000  
REFERENCE : CHIEF RAY

EDMUND OPTICS  
HTTP://WWW.EDMUNDOPTICS.COM  
47636INK  
TUE DEC 16 2008  
MAXIMUM FOCAL SHIFT RANGE: 138.2692 μm  
DIFFRACTION LIMITED RANGE: 7.728 μm  
PUPIL ZONE: 0.0000

EDMUND OPTICS  
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT  
47636INK  
TUE DEC 16 2008  
MAXIMUM SCALE: ± 500.000 μm.  
0.486 0.588 0.656  
SURFACE: IMAGE

EDMUND OPTICS  
HTTP://WWW.EDMUNDOPTICS.COM  
47636INK  
TUE DEC 16 2008  
DATA FOR 0.4250 TO 0.6750 μm.  
SURFACE: IMAGE

EDMUND OPTICS  
HTTP://WWW.EDMUNDOPTICS.COM



www.edmundoptics.com