



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES





SURFACE: IMA
 IMA: 0.000 MM
SPOT DIAGRAM
 47672INK
 TUE DEC 16 2008 UNITS ARE μm .
 FIELD :
 RMS RADIUS : 1.984
 GEO RADIUS : 2.744
 SCALE BAR : 10
 REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47672INK
 TUE DEC 16 2008
 MAXIMUM FOCAL SHIFT RANGE: 273.9150 μm
 DIFFRACTION LIMITED RANGE: 150.388 μm
 PUPIL ZONE: 0.0000

CHROMATIC FOCAL SHIFT

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



TRANSVERSE RAY FAN PLOT
 47672INK
 TUE DEC 16 2008
 MAXIMUM SCALE: $\pm 50.000 \mu\text{m}$.
 0.486 0.588 0.656
 SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47672INK
 TUE DEC 16 2008
 DATA FOR 0.4250 TO 0.6750 μm .
 SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



www.edmundoptics.com