



# TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



SURFACE: INA  
 IDA: 0.000 MM  
**SPOT DIAGRAM**

49343INK  
 TUE DEC 16 2008 UNITS ARE  $\mu\text{m}$ .  
 FIELD : 1  
 RMS RADIUS : 10.123  
 GEO RADIUS : 29.577  
 SCALE BAR : 100



REFERENCE : CHIEF RAY

**EDMUND OPTICS**  
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49343INK  
 TUE DEC 16 2008  
 MAXIMUM FOCAL SHIFT RANGE: 337.7142  $\mu\text{m}$   
 DIFFRACTION LIMITED RANGE: 17.790  $\mu\text{m}$   
 PUPIL ZONE: 0.0000

**CHROMATIC FOCAL SHIFT**

**EDMUND OPTICS**  
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



**TRANSVERSE RAY FAN PLOT**

49343INK  
 TUE DEC 16 2008  
 MAXIMUM SCALE:  $\pm 200.000 \mu\text{m}$ .  
 0.486 0.588 0.656

SURFACE: IMAGE

**EDMUND OPTICS**  
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49343INK  
 TUE DEC 16 2008  
 DATA FOR 0.4000 TO 1.0000  $\mu\text{m}$ .  
 SURFACE: IMAGE

**POLYCHROMATIC DIFFRACTION MTF**

**EDMUND OPTICS**  
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)