




NOTES:

1. SUBSTRATE
BOROFLOAT®
2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)
T(AVG) >80% @ 400 - 550nm
T(AVG) <1.0% @ 640 - 740nm



3. CUT AND SEAM

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION 	TITLE	50 x 50 CYAN DICHROIC FILTER	
SURFACE QUALITY	80-50	80-50		DWG NO	39912	SHEET 1 OF 1
CLEAR APERTURE	≥85 %	≥85 %				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN mm			