





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SHORTPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A | VALUE |
|-------------------------|--------------------|
| CUT-OFF WAVELENGTH | 950±2nm |
| TRANSMISSION WAVELENGTH | 450 - 910nm |
| REJECTION WAVELENGTH | 1025 - 1235nm |
| TRANSMISSION | >85 |
| SURFACE QUALITY | 40-20 |
| COATING TYPE | TRADITIONAL COATED |



ALL DIMS IN mm

| | |
|--------------|---|
| TITLE | M30.5 x 0.5, 950nm MOUNTED SHORTPASS FILTER |
| DWG NO | 66665 |
| SHEET 1 OF 1 | |