




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



REV. A	VALUE
SHAPE	PLANO
TRANSMISSION WAVELENGTH	671 - 790
DURABILITY	MIL-C-48497A
CUT-ON WAVELENGTH	659
SURFACE FLATNESS	>95
SURFACE QUALITY	60-40
CLEAR APERTURE	Ø8.8
BEVEL	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



TITLE	Ø12.5mm, 659nm, DICHROIC LASER BEAM COMBINER	
DWG NO	86388	SHEET 1 OF 1

ALL DIMS IN mm