



NOTES:

- 1. SUBSTRATE
UV GRADE FUSED SILICA
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
HARD COATED
PERFORMANCE SPECS:
T(AVG) = 90% FROM 612 - 950nm @ 45 ° AOI
R(AVG) = 98% FROM 350 - 596nm @ 45 ° AOI
T(ABS) = 50% @ 605nm @ 45 ° AOI



3. FINE GRIND SURFACE

- 4. SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
- 5. TRANSMITTED WAVEFRONT DISTORTION RMS @ 632.8nm ≤1λ
- 6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | | | | | | |
|-----------------|----------------------|----------------------|---|----|--------|-----------------|
| | S1 | S2 |  | | | |
| SHAPE | PLANO | PLANO |  | | | |
| SURFACE QUALITY | 60-40 | 60-40 | | | | |
| CLEAR APERTURE | 22.00 x 32.00 | 22.00 x 32.00 | TITLE | | | |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | 605nm, 25.2 X 35.6mm, DICHROIC FILTER | | | |
| | | | ALL DIMS IN | mm | DWG NO | 86335 |
| | | | | | | SHEET 1 OF 1 |