




NOTES:

- 1. SUBSTRATE:
POLYCARBONATE
- 2. EDGES CUT AND SEAMED
- 3. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | S1 | S2 |
|------------------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| WAVELENGTH RANGE | 400 - 1600nm | 400 - 1600nm |
| DIFFUSING ANGLE (FWHM) | 10 x 60 ±1 x ±6° | 10 x 60 ±1 x ±6° |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |



ALL DIMS IN mm



TITLE 10 x 60° DIFFUSING ANGLE 8" x 8" UNMOUNTED

DWG NO 55445 SHEET 1 OF 1