




NOTES:

1. SUBSTRATE : N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)
 S1: UNCOATED

 S2: LASER V-COAT
 R(abs) <0.25% @ 633nm

 FINE GRIND SURFACE

4. RoHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
ANGLE TOLERANCE (arcsec)	±15	±15
SURFACE QUALITY	40-20	40-20
SURFACE FLATNESS	λ/8	λ/8
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION



ALL DIMS IN

mm

 **Edmund Optics®**

TITLE

25mm, 633 V-COAT, N-BK7 LASER LINE RA PRISM

DWG NO

83217

SHEET
1 OF 1