




NOTES:



- 1. SUBSTRATE : N-BK7
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: UNCOATED

S2: LASER V-COAT
R(abs) <0.25% @ 785nm
- 3. FINE GRIND SURFACE
- 4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
ANGLE TOLERANCE (arcsec)	±15	±15		TITLE	30mm, 785 V-COAT, N-BK7 LASER LINE RA PRISM	
SURFACE QUALITY	40-20	40-20		DWG NO	83226	SHEET 1 OF 1
SURFACE FLATNESS	λ/8	λ/8				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		ALL DIMS IN	mm	