

NOTES:



1. SUBSTRATE MATERIAL:
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Gold
R(avg) >96% @ 700 - 2000
R(avg) >96% @ 2000 - 10000nm

S2: NONE

3. FINE GROUND SURFACE

4. RoHS COMPLIANT



SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	CONCAVE	CONVEX
RADIUS	24mm	24mm
APERTURE	f/1	N/A
EFFECTIVE FOCAL LENGTH	12mm	N/A
FOCAL LENGTH TOLERANCE	±2%	N/A
SURFACE QUALITY	80-50	N/A

THIRD ANGLE PROJECTION

ALL DIMS IN mm

TITLE	12mm Dia. x 12mm FL Protected Gold, Concave Mirror		
DWG NO	43833	SHEET 1 OF 1	