




NOTES:

- 1. SUBSTRATE:  
PMMA
- 2. COATING  
S1 & S2: R(avg) <0.5% @ 450 - 650nm
- 3. FOCAL LENGTH TOLERANCE: ±1%



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

S1		S2		THIRD ANGLE PROJECTION 		TITLE	25.4mm DIA F/10 VIS COATED, MOLDED ACRYLIC ASPHERIC LENS	
SHAPE	CONVEX		PLANO					
BEVEL	PROTECTIVE AS NEEDED		PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	48187	SHEET 1 OF 1

 **Edmund Optics®**