NOTES:


1. COATING (APPLY ACROSS CLEAR APERTURE)

S1: R(abs) 70% ±5% @ 550nm R(abs) 70% ±10% @ 700 - 1100 nm


T(abs) 30% ±5% @ 550nm


T(abs) 30% ±10%@ 700 - 1100nm


FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



S2: R(avg) <1.0% @ 700 - 1100nm R(abs) <2.0% @700 - 1100nm







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2	THIRD ANGLE PROJECTION	TITLE	70R/30T, VIS, C-MOUNTED PLATE BEAMSPLITTER	
SURFACE QUALITY	60-40	60-40	'		DE/ WIGH EITTER	CLIEFT
SURFACE FLATNESS	1λ	1λ	ALL DIMS IN mm	DWG NO	49689	SHEET 1 OF 1