





FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
CLEAR APERTURE	Ø11.50
CENTER WAVELENGTH	658±13.16nm
FULL WIDTH HALF MAX (FWHM)	≤52.64nm
OPTICAL DENSITY	≥6.0
TRANSMISSION	≥85%



THIRD ANGLE PROJECTION		TITLE	658nm, 12.5 mm Dia., OD 6.0 Ultra-Thin Notch Filter	
ALL DIMS IN	mm	DWG NO	14762	SHEET 1 OF 1