
## NOTES:


1. SUBSTRATE: FUSED SILICA (CORNING 7980)


- 2. S2 TO BE PARALLEL WITH S1 TO WITHIN <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: R(AVG) ≤0.5% @ 600 - 1050nm

4. FINE GRIND SURFACE

5. ROHS COMPLIANT







## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2		
SHAPE	PLANO	PLANO		
SURFACE QUALITY	40-20	40-20		
CLEAR APERTURE (mm)	Ø22.50	Ø22.50		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		

				S®	
THIRD ANGLE PROJECTION		TITLE	25mm Dia., 3mm Thick, NIR I Coated, λ/4 Fused Silica Window		
	ALL DIMS IN	mm	DWG NO	18341	SHEET 1 OF 1