


LFV3-G-50BL



Model name	LFV3-G-50BL
LED color	Blue
Input voltage	24 VDC
Power consumption(max.)	15 W
Weight(max.)	285 g
Connector	SMR-03V-B
Polarity and signal	1:(+), 2:NC, 3:(-)

Unit: mm

