

[All Products](#) / [Microscopy](#) / [Finite Conjugate Objectives](#)

Commercial Grade Standard Microscope Objectives



- Achromatic and Plan Designs
- Use with T- and C-Mounting Systems
- Ideal for OEM Applications

Common Specifications

Physical & Mechanical Properties

Maximum Diameter (mm): 24

Threading & Mounting

Mounting Threads: 0.7965-36 TPI, 55° Whitworth

Environmental & Durability Factors

Operating Temperature (°C): 5 to 40

Storage Temperature (°C): -20 to 60

Operating Relative Humidity: 45% to 85%

Technical Information

Products

Magnification	NA	Type	WD (mm)	Stock Number	Price	Buy
4X	0.10	Plan	15.25	#67-706	€128,00	3-4 days
4X	0.10	Achromatic	18.8	#43-902	€91,00	In Stock
10X	0.25	Plan	1.5	#43-907	€159,00	3-4 days
10X	0.25	Achromatic	6.14	#43-903	€106,00	In Stock
40X	0.65	Achromatic, Spring-Loaded	0.48	#43-904	€138,00	In Stock
100X	1.25	Plan, Spring-Loaded	0.1	#43-909	€344,00	3-4 days
100X	1.25	Achromatic, Spring-Loaded	0.1	#43-905	€175,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com