

[All Products](#) / [Microscopy](#) / [Finite Conjugate Objectives](#)

Mitutoyo Telecentric Objectives

 See More by [Mitutoyo](#)


- Long Working Distances Allow for Integration into Machine Vision Measurement Systems
- Compact Design and Long Parfocal Length Simplifies Mounting
- [Tube](#) Available for Use with C-Mount Cameras
- Aluminum Alloy Housing

Common Specifications

General

Note: Image is formed 280mm from specimen (170mm from the mounting flange)

Manufacturer: Mitutoyo

Optical Properties

Wavelength Range (nm): 435 - 655

Parfocal Length (mm): 110

Immersion Liquid: N/A

Sensor

Maximum Sensor Format: 2/3"

Threading & Mounting

Mounting Threads: M26 x 36 TPI

Environmental & Durability Factors

Operating Temperature (°C): +5 to +40

Operating Humidity: 20 - 80%

Technical Information

Products

FL (mm)	Magnification	NA	Type	WD (mm)	Stock Number	Price	Buy
175.08	1X	0.03	Microscope Objective	61	#56-984	€2.455,00	3-4 days
58.51	3X	0.09	Microscope Objective	77	#56-985	€1.330,00	3-4 days
34.74	5X	0.13	Microscope Objective	61	#56-986	€1.135,00	3-4 days
17.50	10X	0.21	Microscope Objective	51	#56-987	€1.380,00	3-4 days
9.21	20X	0.42	Microscope Objective	20	#87-228	€2.970,00	3-4 days
3.61	50X	0.55	Microscope Objective	13	#87-229	€3.990,00	Contact Us
1.79	100X	0.70	Microscope Objective	6	#87-230	€5.310,00	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com