

[All Products](#) / [Microscopy](#) / [Finite Conjugate Objectives](#)

Mitutoyo Compact Objectives

See More by [Mitutoyo](#)



- Long Working Distances Allow for Integration into Machine Vision Measurement Systems
- Small Size with Excellent Performance
- Long Working Distances
- Easily Integrates with C-Mount Cameras

Common Specifications

General			
Manufacturer:		Mitutoyo	
Physical & Mechanical Properties			
Maximum Diameter (mm):		30	
Optical Properties			
Wavelength Range (nm):		435 - 655	Field Number (mm): 24
Parfocal Length (mm):		110	Immersion Liquid: N/A
Sensor			
Maximum Sensor Format:		2/3"	
Threading & Mounting			
Mounting Threads:		M26 x 36 TPI	
Environmental & Durability Factors			
Operating Temperature (°C):		+5 to +35	Operating Humidity: 65±20%

Technical Information

Products

FL (mm)	Magnification	NA	Type	WD (mm)	Stock Number	Price	Buy
58.99	1X	0.03	Microscope Objective	73.7	#56-988	€666,74	20+ In Stock
60.33	2X	0.06	Microscope Objective	92.0	#56-989	€666,74	5 In Stock
50.61	3X	0.07	Microscope Objective	77.8	#56-990	€711,26	Contact Us



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com