

[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Iris Diaphragms](#)

High Performance Standard Series Iris Diaphragms



- Corrosion and High Temperature Resistance Housing
- Anti-Reflective (AR) Spring Steel or Burnished Spring Steel Leaf Options Available
- Mounted Version Features both an English and Metric Tapped Hole for Easy Post Mounting

Technical Information

Products

Type	Minimum Aperture (mm)	Maximum Aperture (mm)	Outer Diameter (mm)	Number of Leaves	Stock Number	Price	Buy
Unmounted	0.5, Typical	5.0	10.0	8.00	#57-573	€106,00 Qty 5+ €93,60	3-4 days
Unmounted	0.5, Typical	7.0	12.0	8.00	#57-574	€106,00 Qty 5+ €93,60	3-4 days
Unmounted	0.8, Typical	8	14.8	8	#64-507	€72,00 Qty 5+ €63,50	3-4 days
Unmounted	1.0, Typical	12.0	19.8	11.00	#57-575	€72,00 Qty 5+ €63,50	3-4 days
Unmounted	1.0, Typical	18.0	28.0	12.00	#57-576	€72,00 Qty 5+ €63,50	3-4 days
Unmounted	1.2, Typical	20.0	30.0	12.00	#57-577	€88,50 Qty 5+ €78,40	3-4 days
Unmounted	1.5, Typical	25.00	37.0	15.00	#84-131	€88,50 Qty 5+ €78,40	3-4 days
Unmounted	0.5, Typical	5.0	10.0	8.00	#57-578	€106,00 Qty 5+ €93,60	3-4 days
Unmounted	0.5, Typical	7.0	12.0	8.00	#57-579	€106,00 Qty 5+ €93,60	3-4 days
Unmounted	1.0, Typical	8.0	14.8	9	#57-580	€72,00 Qty 5+ €63,50	3-4 days
Unmounted	1.0, Typical	12.0	19.8	11.00	#57-581	€72,00 Qty 5+ €63,50	Contact Us
Unmounted	1.2, Typical	20.0	30.0	12.00	#64-508	€88,50 Qty 5+ €78,40	In Stock
Unmounted	1.5, Typical	25.0	37.0	15.00	#57-582	€88,50 Qty 5+ €78,40	In Stock
Unmounted	2.5, Typical	37.0	53.0	16.00	#57-583	€88,50 Qty 5+ €78,40	In Stock
Unmounted	2.5, Typical	50.0	70.0	18.00	#57-584	€183,00 Qty 5+ €161,90	Contact Us
Unmounted	4.0, Typical	60.0	82.0	17.00	#57-585	€209,00 Qty 5+ €184,30	3-4 days

Unmounted	4.0, Typical	75.0	100.0	20.00	#57-586	€314,00 Qty 5+ €276,80	3-4 days
Mounted	0.5, Typical	5.0	26.5	8.00	#23-255	€122,00 Qty 5+ €107,50	Contact Us
Mounted	0.5, Typical	7.0	26.5	8.00	#23-256	€122,00 Qty 5+ €107,50	3-4 days
Mounted	0.8, Typical	8.0	26.5	8.00	#23-257	€88,50 Qty 5+ €78,00	3-4 days
Mounted	1.0, Typical	12.0	39.0	11.00	#23-258	€88,50 Qty 5+ €78,00	3-4 days
Mounted	1.0, Typical	18.0	52.0	12.00	#23-259	€88,50 Qty 5+ €78,00	3-4 days
Mounted	1.2, Typical	20.0	52.0	12.00	#23-260	€104,00 Qty 5+ €91,60	3-4 days
Mounted	1.5, Typical	25.0	52.0	15.00	#23-261	€104,00 Qty 5+ €91,60	3-4 days
Mounted	0.5, Typical	7.0	26.5	8.00	#23-262	€122,00 Qty 5+ €107,50	3-4 days
Mounted	1.0, Typical	8.0	26.5	9.00	#23-263	€88,50 Qty 5+ €78,00	3-4 days
Mounted	1.0, Typical	12.0	39.0	11.00	#23-264	€88,50 Qty 5+ €78,00	3-4 days
Mounted	1.2, Typical	20.0	52.0	12.00	#23-265	€104,00 Qty 5+ €91,60	3-4 days
Mounted	1.5, Typical	25.0	52.0	15.00	#23-266	€104,00 Qty 5+ €91,60	3-4 days
Mounted	2.5, Typical	50.0	90.0	18.00	#23-267	€195,00 Qty 5+ €171,70	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com