

[All Products](#) / [Test Targets](#) / [Color & Gray Level Test Targets](#)

# Spectralon® White Balance and Diffuse Reflectance Targets



- Diffuse Reflectance with 99% Nominal Reflectance in UV-VIS-NIR Wavelength Range (350 - 1600nm)
- Durable, Stable, and Washable
- NIST Traceable Calibration Certificate and Data from 250 - 2500nm

## Common Specifications

<b>NIST Certification:</b>	Yes
<b>Nominal Reflectance (%):</b>	99
<b>Mounting:</b>	Rugged Anodized Aluminum
<b>Reflective Material:</b>	Spectralon®
<b>Operating Temperature (°C):</b>	-80 to 350
<b>Operating Relative Humidity:</b>	5% - 95%

# Technical Information

## Products

Title	Stock Number	Price	Buy
2" Spectralon® White Balance and Diffuse Reflectance Targets	<a href="#">#58-609</a>	€1.195,00 <a href="#">Volume Pricing</a>	12 In Stock
5" Spectralon® White Balance and Diffuse Reflectance Targets	<a href="#">#58-610</a>	€1.495,00 <a href="#">Volume Pricing</a>	10 In Stock
10" Spectralon® White Balance and Diffuse Reflectance Targets	<a href="#">#58-611</a>	€2.795,00 <a href="#">Volume Pricing</a>	Contact Us
12" Spectralon® White Balance and Diffuse Reflectance Targets	<a href="#">#58-612</a>	€3.295,00 <a href="#">Volume Pricing</a>	3 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)