

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Plastic Molded](#)

Molded Acrylic Aspheric Lenses



- Prescription Information Available
- Reduced Spherical Aberration
- Broadband AR Coating Option

Common Specifications

Optical Properties

Substrate: PMMA	Focal Length Tolerance (%) : ±1
Aspheric Design Wavelength (nm) : 632.8	

Technical Information

Products

Dia. (mm)	EFL (mm)	NA	Coating	Stock Number	Price	Buy
12.70	12.70	0.50	Uncoated	#48-164	€54,00 Qty 11+ €45,00	3-4 days
12.70	25.40	0.25	Uncoated	#48-165	€57,00 Qty 11+ €47,50	In Stock
12.70	50.80	0.13	Uncoated	#48-166	€54,00 Qty 11+ €45,00	3-4 days
#48-169 Clearance						
 Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.						
12.70	127.00	0.05	Uncoated		€52,00	3-4 days
25.40	25.40	0.50	Uncoated	#48-170	€61,50 Qty 11+ €51,00	In Stock
25.40	50.80	0.25	Uncoated	#48-171	€61,50 Qty 11+ €51,00	3-4 days
25.40	102.00	0.12	Uncoated	#48-172	€57,00 Qty 11+ €47,50	3-4 days
25.40	152.00	0.08	Uncoated	#48-173	€57,00 Qty 11+ €47,50	3-4 days
25.40	203.00	0.06	Uncoated	#48-174	€57,00 Qty 11+ €47,50	3-4 days
25.40	254.00	0.05	Uncoated	#48-175	€57,00 Qty 11+ €47,50	In Stock
12.70	12.70	0.50	BBAR (450-650nm)	#48-176	€62,50 Qty 11+ €52,00	3-4 days

12.70	25.40	0.25	BBAR (450-650nm)	#48-177	€62,50 Qty 11+ €52,00	In Stock
12.70	50.80	0.13	BBAR (450-650nm)	#48-178	€62,50 Qty 11+ €52,00	3-4 days
25.40	25.40	0.50	BBAR (450-650nm)	#48-182	€67,50 Qty 11+ €55,50	3-4 days
25.40	50.80	0.25	BBAR (450-650nm)	#48-183	€67,50 Qty 11+ €55,50	3-4 days
25.40	102.00	0.12	BBAR (450-650nm)	#48-184	€67,50 Qty 11+ €55,50	3-4 days
25.40	152.00	0.08	BBAR (450-650nm)	#48-185	€67,50 Qty 11+ €55,50	3-4 days
25.40	203.00	0.06	BBAR (450-650nm)	#48-186	€67,50 Qty 11+ €55,50	3-4 days
25.40	254.00	0.05	BBAR (450-650nm)	#48-187	€67,50 Qty 11+ €55,50	3-4 days
12.70	12.70	0.50	BBAR (700-1100nm)	#64-580	€62,50 Qty 11+ €52,00	3-4 days
12.70	25.40	0.25	BBAR (700-1100nm)	#64-581	€62,50 Qty 11+ €52,00	3-4 days
12.70	50.80	0.13	BBAR (700-1100nm)	#64-582	€62,50 Qty 11+ €52,00	3-4 days
25.40	25.40	0.50	BBAR (700-1100nm)	#64-586	€67,50 Qty 11+ €55,50	3-4 days
25.40	50.80	0.25	BBAR (700-1100nm)	#64-587	€67,50 Qty 11+ €55,50	3-4 days
25.40	102.00	0.12	BBAR (700-1100nm)	#64-588	€67,50 Qty 11+ €55,50	3-4 days

12.70	6.40	1.00	Uncoated	#33-255	€57,00 Qty 11+ €47,50	3-4 days
12.70	9.50	0.67	Uncoated	#33-256	€57,00 Qty 11+ €47,50	3-4 days
25.40	12.70	1.00	Uncoated	#33-257	€62,50 Qty 11+ €52,00	3-4 days
25.40	19.10	0.67	Uncoated	#33-258	€62,50 Qty 11+ €52,00	3-4 days
12.70	6.40	1.00	BBAR (450-650nm)	#33-259	€67,50 Qty 11+ €55,50	3-4 days
12.70	9.50	0.67	BBAR (450-650nm)	#33-260	€67,50 Qty 11+ €55,50	3-4 days
25.40	12.70	1.00	BBAR (450-650nm)	#33-261	€73,00 Qty 11+ €60,50	3-4 days
25.40	19.10	0.67	BBAR (450-650nm)	#33-262	€73,00 Qty 11+ €60,50	3-4 days
12.70	6.40	1.00	BBAR (700-1100nm)	#33-263	€67,50 Qty 11+ €55,50	3-4 days
12.70	9.50	0.67	BBAR (700-1100nm)	#33-264	€67,50 Qty 11+ €55,50	3-4 days
25.40	12.70	1.00	BBAR (700-1100nm)	#33-265	€73,00 Qty 11+ €60,50	3-4 days
25.40	19.10	0.67	BBAR (700-1100nm)	#33-266	€73,00 Qty 11+ €60,50	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com