

[All Products](#) / [Imaging Lenses](#) / [M12 Lenses \(S-Mount Lenses\)](#)
TECHSPEC® HEO Series M12 Lenses


- Up to 1/2", S-Mount Lens
- Up to 1.2 MegaPixels, 5µm Pixel Size Sensors
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- 2.2mm to 8mm Focal Length

Common Specifications

General

IR Cut Filter:

No

Imaging Lens Type:

Meets IEC IPX7 and IPX9K

Physical & Mechanical Properties

Iris Option:

Fixed

Weight (g):

4

Optical Properties

Working Distance (mm):

400 - ∞

Threading & Mounting

Mount:

M12 x 0.5 (S-Mount)

Technical Information

Products

FL (mm)	Aperture (f/#)	Max. Sensor Format	WD (mm)	IR Cut Filter	Stock Number	Price	Buy
2.20	f/2	1/3"	400 - ∞	No	#58-840	€159,00	3-4 days
3.60	f/2.5	1/3"	400 - ∞	No	#58-841	€159,00	3-4 days
8.00	f/2.5	1/2"	400 - ∞	No	#63-759	€159,00	3-4 days
2.20	f/2	1/3"	400 - ∞	No	#58-844	€159,00	3-4 days
3.60	f/2.5	1/3"	400 - ∞	No	#58-845	€159,00	3-4 days
8.00	f/2.5	1/2"	400 - ∞	No	#63-761	€159,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com