

[All Products](#) / [Test Targets](#) / [Resolution Test Targets](#)

USAF Pattern Wheel Target



- Tests Resolutions from 4 to 228 lp/mm
- Ability to tests Multiple Field Points using 9 Targets
- Reduces Testing Time

Common Specifications

Physical & Mechanical Properties




Thickness (mm):	1.50	Parallelism (inches):	<0.0005 per inch
Line Width Tolerance (mm):	±0.0005		

Optical Properties

Coating:	First Surface Reflective Chromium		
Substrate:	Float Glass	Resolution:	Minimum: Group 2 Element 1 Maximum: Group 7 Element 6
Surface Quality:	20-10	Surface Flatness (P-V):	2λ

Technical Information

Products

Title	Stock Number	Price	Buy
#59-203 Clearance			
 1" x 3" Positive, USAF Wheel Target	 Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€379,04 Volume Pricing	1 In Stock
<hr/>			
1" x 3" Negative, USAF Wheel Target	#59-204	€379,04 Volume Pricing	5 In Stock
<hr/>			
#59-205 Clearance			
 1" x 1" Positive, USAF Wheel Target	 Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€379,04 Volume Pricing	4 In Stock
<hr/>			
#59-207 Clearance			
 1.5" Dia. Negative, USAF Wheel Target	 Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€379,04 Volume Pricing	5 In Stock
<hr/>			



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com