

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Infrared](#)

LightPath® Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses

See More by [Lightpath®](#)



- Wavelength Range of 1.8 - 12 μ m
- Variety of Coating Options
- Mounted and Unmounted Versions




Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed
--------	----------------------

Optical Properties			
Substrate:	Black Diamond™ BD-2 (Ge ₂₈ Sb ₁₂ Se ₆₀)		
Surface Quality:	80-50	Index of Refraction (n _d) @ 10μm:	2.6023
Index of Refraction (n _d) @ 14μm:	2.5843	Index of Refraction (n _d) @ 4μm:	2.6210
Index of Refraction (n _d) @ 5μm:	2.6173	Conjugate Distance:	Infinite
Material Properties			
Density (g/cm ³):	4.68	Thermo-optic coefficient dn/dT:	70 x 10 ⁻⁶ /°C from -40° to +80°C (5 - 14 μm)
Transformation Temperature (°C):	285.00		

Technical Information



Products

Dia. (mm)	EFL (mm)	NA	Coating	Stock Number	Price	Buy
6.50	4.00	0.56	BBAR (1800-3000nm)	#66-560	€385,22 Volume Pricing	9 In Stock
6.50	4.00	0.56	BBAR (3000-5000nm)	#66-561	€385,22 Volume Pricing	2 In Stock
8.00	5.95	0.56	BBAR (3000-5000nm)	#87-178	€438,78 Volume Pricing	17 In Stock
3.50	1.50	0.72	BBAR (1800-3000nm)	#83-717	€385,22 Volume Pricing	15 In Stock
3.50	1.50	0.72	BBAR (3000-5000nm)	#83-718	€385,22 Volume Pricing	17 In Stock
4.50	1.47	0.83	BBAR (8000-12000nm)	#88-073	€385,22 Volume Pricing	3 In Stock
#66-564 Clearance						
 Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.						
5.50	1.87	0.85	BBAR (1800-3000nm)		€217,28	1 In Stock
5.50	1.87	0.85	BBAR (8000-12000nm)	#66-566	€385,22 Volume Pricing	20+ In Stock
6.50	4.00	0.56	BBAR (3000-5000nm)	#66-569	€385,22 Volume Pricing	20+ In Stock

[#88-080 Clearance](#)



Clearance

9.25	3.00	0.71	BBAR (1800-3000nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€242,00	3 In Stock
------	------	------	-----------------------	--	---------	------------

[#83-721 Clearance](#)



Clearance

6.24	1.50	0.72	BBAR (1800-3000nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€205,95	1 In Stock
------	------	------	-----------------------	--	---------	------------

[#88-077 Clearance](#)



Clearance

8.24	1.47	0.83	BBAR (1800-3000nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€205,95	3 In Stock
------	------	------	-----------------------	--	---------	------------

[#88-079 Clearance](#)



Clearance

8.24	1.47	0.83	BBAR (8000- 12000nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€177,11	20+ In Stock
------	------	------	----------------------------	--	---------	--------------

[#66-572 Clearance](#)



Clearance

5.50	1.87	0.85	BBAR (1800- 3000nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€242,00	2 In Stock
------	------	------	---------------------------	--	---------	------------



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
Phone: 1-800-363-1992 :
www.edmundoptics.com