

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Inline Lights](#)

Advanced Illumination In-Line Lights See More by [Advanced Illumination](#)



- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
- Multiple Versions Offered

Common Specifications

General

LED Lifetime (hours): 50,000	Number of LEDs: 1 High Brightness
Type of Illumination: LED Illuminator	Manufacturer: Advanced Illumination
Geometry: Spot Light	

Physical & Mechanical Properties

Weight (g): 42.5

Optical Properties

Light Distribution (%): ±10

Hardware & Interface Connectivity

Connector: Flying Leads

Power Supply: Power Supply Required and Sold Separately:
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

Length of Cable (m): 1.5

Environmental & Durability Factors

Operating Temperature (°C): 0 to 60

Technical Information

Products

Color	Wavelength (nm)	Stock Number	Price	Buy
White	-	#66-861	€540,00	8 In Stock
White	-	#83-302	€660,00	Contact Us
Blue	470	#66-862	€540,00	2 In Stock
Blue	470	#83-303	€660,00	Contact Us
Green	530	#66-863	€540,00	1 In Stock
Green	530	#83-304	€660,00	Contact Us
Yellow	590	#66-864	€540,00	Contact Us
Yellow	590	#83-305	€660,00	Contact Us
Red	625	#66-865	€540,00	2 In Stock
Red	625	#83-306	€660,00	Contact Us



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
Phone: 1-800-363-1992 :
www.edmundoptics.com