

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

Ultra High Resolution Fixed Focal Length Lenses



- 2/3", C-Mount Lens
- Up to 10 MegaPixels, 2.4µm Pixel Size Sensors
- Spectral Range of 400 - 1000nm
- 8mm to 50mm Focal Lengths

Common Specifications

Physical & Mechanical Properties

Iris Option: Variable

Optical Properties

Maximum Image Circle (mm): 11.00

Working Distance (mm): 100 - ∞

Sensor

Maximum Sensor Format: 2/3"

Threading & Mounting

Mount: C-Mount

Technical Information

Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
5.00	2/3"	f/1.8 - f/16	100 - ∞	C- Mount	#68-681	€1.915,00	3-4 days
8.50	2/3"	f/1.8 - f/22	100 - ∞	C- Mount	#68-682	€1.640,00	3-4 days
12.00	2/3"	f/1.8 - f/11	100 - ∞	C- Mount	#68-683	€1.590,00	Contact Us
16.00	2/3"	f/1.8 - f/16	100 - ∞	C- Mount	#68-684	€1.590,00	3-4 days
25.00	2/3"	f/1.8 - f/16	100 - ∞	C- Mount	#68-685	€1.470,00	3-4 days
35.00	2/3"	f/2 - f/16	100 - ∞	C- Mount	#68-686	€1.470,00	3-4 days
50.00	2/3"	f/2.8 - f/16	100 - ∞	C- Mount	#68-687	€1.505,00	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com