

[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Shutters](#)

## C and T-Mount Motorized Shutters

- Male and Female C- and T-Threads for Easy Integration
- Simple On/Off Operation with TTL Input
- M6 and 1/4-20 Tapped Holes for Post Mounting



### Common Specifications

#### General

Deactivation time (ms): 50

Function: Shutter

#### Electrical

Coil Resistance ( $\Omega$ ): 90 @ 25°C

Coil Resistance Tolerance (%):  $\pm 10$

#### Hardware & Interface Connectivity

Operating Voltage (V): 4.5 V ~ 5.5 V DC

#### Threading & Mounting

Compatible Post: M6 x 1.0, 1/4-20

## Technical Information

# Products

Function	Aperture (mm)	Mount	Stock Number	Price	Buy
Shutter	30.0	T-Mount	<a href="#">#11-153</a>	€798,25 <a href="#">Volume Pricing</a>	10 In Stock
Shutter	20.0	C-Mount	<a href="#">#87-208</a>	€602,55 <a href="#">Volume Pricing</a>	15 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)