

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Gas Lasers](#)

Lasos Helium-Neon Lasers



- Excellent Stability
- Long Lifetime
- Precise Alignment

Common Specifications

General	
Type of Laser:	HeNe
Optical Properties	
Wavelength (nm):	632.80

Technical Information

Products

Wavelength (nm)	Output Power (mW)	Beam Diameter (mm)	Beam Divergence (mrad)	Polarization	Longitudinal Mode Spacing, Nominal (MHz)	Stock Number	Price	Buy
632.80	20	1.00	≤1.0	Random	257.00	#35-217	€1.780,00	1 In Stock
632.80	18	1.00	≤1.0	≥500:1	257.00	#35-216	€1.365,00	1 In Stock
632.80	18	1.00	≤1.0	Random	257.00	#35-215	€1.475,00	Contact Us
632.80	15	1.00	≤1.0	≥500:1	257.00	#35-214	€1.450,00	1 In Stock
632.80	15	1.00	≤1.0	Random	257.00	#35-213	€1.600,00	1 In Stock
632.80	10	0.7	≤1.4	≥500:1	320.00	#35-212	€1.270,00	1 In Stock
632.80	10	0.7	≤1.4	Random	320.00	#35-211	€1.300,00	1 In Stock
632.80	5	0.8	≤1.1	≥500:1	438.00	#35-210	€780,00	2 In Stock
632.80	5	0.8	≤1.1	Random	438.00	#35-209	€700,00	1 In Stock
632.80	2	0.75	≤1.2	≥500:1	614.00	#35-208	€595,00	3 In Stock
632.80	2	0.75	≤1.2	Random	614.00	#35-207	€475,00	1 In Stock
632.80	0.6	0.49	≤1.70	Random	1086.00	#35-206	€475,00	1 In Stock
632.80	0.5	0.49	≤1.75	≥200:1	1086.00	#35-205	€560,00	1 In Stock
632.80	0.5	0.49	≤1.75	≥200:1	1086.00	#35-205- RCD- 05P	€703,80	Contact Us

