

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Industrial and Pointing Lasers](#)

# DPSS Pointing Lasers



- TTL Modulation up to 10kHz
- Transverse Mode TEM<sub>00</sub>
- Blue, Green, Yellow, and IR Output Wavelengths
- TEC or Heatsink Required for Operation ([Sold Separately](#))



## Common Specifications

### Optical Properties

Spatial Mode:	TEM <sub>00</sub>
---------------	-------------------

### Environmental & Durability Factors

Operating Temperature (°C):	23 to 27
-----------------------------	----------

**Technical Information**

Products

Wavelength (nm)	Output Power (mW)	Beam Diameter (mm)	Beam Divergence (mrad)	Stock Number	Price	Buy
473.00	10	1.5	<1.5	<a href="#">#19-469</a>	€1.305,00 <a href="#">Volume Pricing</a>	1 In Stock
520.00	1	3.5	<1	<a href="#">#29-130</a>	€337,00 <a href="#">Volume Pricing</a>	1 In Stock
520.00	5	3.5	<1	<a href="#">#29-131</a>	€355,00 <a href="#">Volume Pricing</a>	1 In Stock
520.00	10	3.5	<1	<a href="#">#29-132</a>	€371,00 <a href="#">Volume Pricing</a>	1 In Stock
520.00	25	3.5	<1	<a href="#">#29-133</a>	€535,00 <a href="#">Volume Pricing</a>	1 In Stock
520.00	50	3.5	<1	<a href="#">#29-134</a>	€705,00 <a href="#">Volume Pricing</a>	1 In Stock
532.00	1	1.0	<1	<a href="#">#37-026</a>	€337,00 <a href="#">Volume Pricing</a>	13 In Stock
532.00	5	1.0	<1	<a href="#">#37-027</a>	€355,00 <a href="#">Volume Pricing</a>	8 In Stock
532.00	10	1.0	<1	<a href="#">#37-028</a>	€371,00 <a href="#">Volume Pricing</a>	7 In Stock
532.00	25	1.5	<1.5	<a href="#">#19-470</a>	€535,00 <a href="#">Volume Pricing</a>	1 In Stock
532.00	80	1.5	<1.5	<a href="#">#19-471</a>	€705,00 <a href="#">Volume Pricing</a>	7 In Stock
589.00	10	1.5	<1.5	<a href="#">#19-472</a>	€1.635,00 <a href="#">Volume Pricing</a>	3 In Stock
1,064.00	1	1.0	<1	<a href="#">#37-041</a>	€337,00 <a href="#">Volume Pricing</a>	5 In Stock

[#37-041-RCD-05P Recertified](#)



Recertified

Stock No.: 37-041-RCD-05P  
Recertified Code: 05P (All Original  
Parts Included, Perfect)

Recertified  
Products

*Typically 1-2 Recertified Products are  
in stock at a time. Please contact our  
sales team if you would like exact  
availability of an item.*

Recertified products are those  
identified with the recertified logo  
indicating they were returned to  
Edmund Optics® and cannot be sold

as new for the following reasons:

- Open Box – Missing original packaging
- Cosmetic Blemishes – Scratches, rub marks or other minor cosmetic imperfections
- Service/Repair – Product has been serviced to the factory original specification
- Factory Returns – Product has been returned in its original condition

Recertified products are inspected for damage and any necessary repairs are made. Products are then certified by Edmund Optics® to be in good working order. Since quantity is low, recertified products are sold on a first come, first serve basis. Any imperfections will be listed in the description, indicated in the stock number, and categorized by the table below. When purchasing recertified products, the Edmund Optics® standard [return policy](#) applies.

View all our [recertified products](#) in the Web Specials section of our website.

1,064.00      1      1.0      <1      €376,56      1 In Stock

Parts		Cosmetic	
05	All Original Parts Included	P	Perfect
04	Missing Manual	N	Minor Defect/Scratches
03	Missing Manual and Small Accessory	J	Major Defect/Scratches
02	Missing Manual and Large Accessory		

1,064.00	5	1.0	<1	<a href="#">#37-042</a>	€355,00 <a href="#">Volume Pricing</a>	11 In Stock
1,064.00	10	1.0	<1	<a href="#">#37-043</a>	€371,00 <a href="#">Volume Pricing</a>	Contact Us
1,064.00	25	1.5	<1.5	<a href="#">#19-473</a>	€535,00 <a href="#">Volume Pricing</a>	5 In Stock
1,064.00	100	1.5	<1.5	<a href="#">#19-474</a>	€705,00 <a href="#">Volume Pricing</a>	6 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)