

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Inline Lights](#)

Advanced Illumination MicroBrite Spot Lights See More by [Advanced Illumination](#)



- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Port
- IP65 Rated - Protection from Dust and Water Spray
- 50,000 Hour Lifetime

Common Specifications

General

Type of Illumination:	LED Illuminator	Manufacturer:	Advanced Illumination
Geometry:	Spot Light	Illumination Mode:	Constant

Physical & Mechanical Properties

Diameter (mm):	7.90	Fiber Bundle Diameter (inches):	1/4
Length (mm):	38.10	Outer Diameter (inches):	0.312

Hardware & Interface Connectivity

Connector:	Flying Leads	Power Supply:	Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Length of Cable (m):	2		

Technical Information

Products

Color	Wavelength (nm)	Dia. (mm)	Stock Number	Price	Buy
White	-	7.90	#34-217	€352,00	In Stock
Blue	470.00	7.90	#34-218	€352,00	In Stock
Green	530.00	7.90	#34-219	€352,00	3-4 days
Red	625.00	7.90	#34-220	€352,00	3-4 days
UV	365.00	7.90	#18-599	€350,00	3-4 days
IR	850.00	7.90	#18-600	€350,00	In Stock
IR	940.00	7.90	#18-601	€350,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com