

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® Liquid Lens Cx Series Fixed Focal Length Lenses



- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Liquid Lens Provides Dynamic Autofocus
- 12mm to 50mm Focal Length

Common Specifications

Physical & Mechanical Properties

Iris Option: Fixed

Optical Properties

Coating Specification: 425 - 675nm BBAR

Threading & Mounting

Filter Thread: M25.5 x 0.50 (Male)

Mount: C-Mount

Environmental & Durability Factors

Storage Temperature (°C):

-20 to +60 For questions regarding operating temperature please contact our support team

Technical Information

Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
12.00	1/2"	f/6	100 - ∞	C- Mount	#33-632	€360,00	In Stock
16.00	2/3"	f/5	100 - ∞	C- Mount	#33-646	€360,00	In Stock
25.00	2/3"	f/5	150 - ∞	C- Mount	#33-661	€360,00	In Stock
35.00	2/3"	f/7	225 - ∞	C- Mount	#33-677	€360,00	In Stock
35.00	2/3"	f/5	225 - ∞	C- Mount	#33-676	€380,00	In Stock
50.00	2/3"	f/7	250 - ∞	C- Mount	#33-687	€445,00	In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com