

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Precision Polished Metal Coatings](#)
TECHSPEC® ZERODUR® $\lambda/10$ First Surface Mirrors See More by [SCHOTT Optical Components](#)


- Precision ZERODUR® Substrates
- $\lambda/10$ Flatness
- Low Coefficient of Thermal Expansion

Common Specifications

Physical & Mechanical Properties

Back Surface:	Commercial Polish	Bevel:	Protective bevel as needed
Clear Aperture (%):	90	Edges:	Ground
Parallelism (arcsec):	30		

Optical Properties

Surface Flatness (P-V):	$\lambda/10$		
Substrate:	ZERODUR®	Surface Quality:	20-10
Coating Type:	Metal		

Material Properties

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):	0.1
--	-----

Technical Information

Products

Dia. (mm)	Surface Flatness (P-V)	Dimensions (mm)	Coating Specification	Coating	Thickness (mm)	Stock Number	Price	Buy
5.00	λ/10	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#17-718	€89,50 Qty 6+ €71,50	3-4 days
#17-719 New								
 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!								
5.00	λ/10	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00		€89,50 Qty 6+ €71,50	3-4 days
#17-720 New								
 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!								
5.00	λ/10	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00		€114,00 Qty 6+ €91,00	3-4 days
#17-721								
5.00	λ/10	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00		€106,00 Qty 6+ €85,00	3-4 days

[#17-722 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	$\lambda/10$	5.0 x 5.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	€89,50 Qty 6+ €71,50	Contact Us
---	--------------	-----------	--------------------------------	-------------------------------	------	-------------------------	------------

[#17-723 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	$\lambda/10$	5.0 x 5.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	€89,50 Qty 6+ €71,50	3-4 days
---	--------------	-----------	--	-------------------------------	------	-------------------------	----------

[#17-724 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	$\lambda/10$	5.0 x 5.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00		€114,00 Qty 6+ €91,00	3-4 days
---	--------------	-----------	---	------------------------------	------	--	--------------------------	----------

[#17-725 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	$\lambda/10$	5.0 x 5.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00		€106,00 Qty 6+ €85,00	Contact Us
---	--------------	-----------	---	--------------------------------	------	--	--------------------------	------------

10.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#39-846	€89,50 Qty 6+ €71,50	Contact Us
-------	--------------	---	--------------------------------	-------------------------------	------	-------------------------	-------------------------	------------

10.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#24-265	€89,50 Qty 6+ €71,50	3-4 days
-------	--------------	---	--	-------------------------------	------	-------------------------	-------------------------	----------

10.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#39-874	€106,00 Qty 6+ €85,00	3-4 days
-------	--------------	---	---	--------------------------------	------	-------------------------	--------------------------	----------

10.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#39-860	€114,00 Qty 6+ €91,00	3-4 days
-	$\lambda/10$	10.0 x 10.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#39-847	€89,50 Qty 6+ €71,50	Contact Us
-	$\lambda/10$	10.0 x 10.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#24-266	€89,50 Qty 6+ €71,50	Contact Us
-	$\lambda/10$	10.0 x 10.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#39-875	€106,00 Qty 6+ €85,00	3-4 days
-	$\lambda/10$	10.0 x 10.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#39-861	€114,00 Qty 6+ €91,00	3-4 days
12.50	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#17-735	€110,00 Qty 6+ €88,00	Contact Us
#17-734 New								
 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!								
12.50	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00		€121,00 Qty 6+ €97,00	3-4 days
12.50	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#17-732	€92,00 Qty 6+ €73,50	3-4 days

[#17-733 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

12.50	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00		€92,00 Qty 6+ €73,50	3-4 days
-------	--------------	---	--	-------------------------------	------	--	-------------------------	----------

-	$\lambda/10$	12.5 x 12.5	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#17-736	€92,00 Qty 6+ €73,50	Contact Us
---	--------------	-------------	--------------------------------	-------------------------------	------	-------------------------	-------------------------	------------

[#17-737 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	$\lambda/10$	12.5 x 12.5	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00		€92,00 Qty 6+ €73,50	3-4 days
---	--------------	-------------	--	-------------------------------	------	--	-------------------------	----------

-	$\lambda/10$	12.5 x 12.5	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#17-739	€110,00 Qty 6+ €88,00	3-4 days
---	--------------	-------------	---	--------------------------------	------	-------------------------	--------------------------	----------

[#17-738 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	$\lambda/10$	12.5 x 12.5	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	3.00		€121,00 Qty 6+ €97,00	3-4 days
15.00	$\lambda/10$	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	3.00	#39-848	€95,00 Qty 6+ €76,00	3-4 days
15.00	$\lambda/10$	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250-700nm)	3.00	#24-267	€95,00 Qty 6+ €76,00	3-4 days
15.00	$\lambda/10$	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	3.00	#39-876	€114,00 Qty 6+ €91,00	3-4 days
15.00	$\lambda/10$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	3.00	#39-862	€125,00 Qty 6+ €100,00	3-4 days
-	$\lambda/10$	15.0 x 15.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450-650nm)	3.00	#39-849	€95,00 Qty 6+ €76,00	3-4 days
-	$\lambda/10$	15.0 x 15.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250-700nm)	3.00	#24-268	€95,00 Qty 6+ €76,00	3-4 days
-	$\lambda/10$	15.0 x 15.0	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450-10000nm)	3.00	#39-877	€114,00 Qty 6+ €91,00	3-4 days
-	$\lambda/10$	15.0 x 15.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700-10000nm)	3.00	#39-863	€125,00 Qty 6+ €100,00	Contact Us

20.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#39-850	€106,00 Qty 6+ €85,00	3-4 days
20.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#24-269	€106,00 Qty 6+ €85,00	3-4 days
20.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#39-883	€128,00 Qty 6+ €102,50	Contact Us
20.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#39-864	€139,00 Qty 6+ €111,00	In Stock
-	$\lambda/10$	20.0 x 20.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#39-851	€106,00 Qty 6+ €85,00	3-4 days
-	$\lambda/10$	20.0 x 20.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#24-270	€106,00 Qty 6+ €85,00	3-4 days
-	$\lambda/10$	20.0 x 20.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#39-909	€128,00 Qty 6+ €102,50	3-4 days
-	$\lambda/10$	20.0 x 20.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#39-865	€139,00 Qty 6+ €111,00	3-4 days
25.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	4.00	#39-852	€114,00 Qty 6+ €91,00	Contact Us
25.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	4.00	#24-271	€114,00 Qty 6+ €91,00	3-4 days
25.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	4.00	#39-910	€135,00 Qty 6+ €108,00	Contact Us
25.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	4.00	#39-866	€147,00 Qty 6+ €117,50	Contact Us

-	$\lambda/10$	25.0 x 25.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	4.00	#39-853	€114,00 Qty 6+ €91,00	Contact Us
-	$\lambda/10$	25.0 x 25.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	4.00	#24-272	€114,00 Qty 6+ €91,00	Contact Us
-	$\lambda/10$	25.0 x 25.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	4.00	#39-911	€135,00 Qty 6+ €108,00	3-4 days
-	$\lambda/10$	25.0 x 25.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	4.00	#39-867	€147,00 Qty 6+ €117,50	3-4 days

[#29-303 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	$\lambda/10$	25.0 x 35.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00		€173,00 Qty 6+ €138,50	3-4 days
---	--------------	-------------	---	------------------------------	------	--	---------------------------	----------

[#29-304 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	$\lambda/10$	25.0 x 35.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00		€152,00 Qty 6+ €121,50	3-4 days
---	--------------	-------------	---	--------------------------------	------	--	---------------------------	----------

[#29-305 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	$\lambda/10$	25.0 x 35.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	€131,00 Qty 6+ €105,00	3-4 days
---	--------------	-------------	--------------------------------	-------------------------------	------	---------------------------	----------

[#29-306 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	$\lambda/10$	25.0 x 35.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	€131,00 Qty 6+ €105,00	3-4 days
---	--------------	-------------	--	-------------------------------	------	---------------------------	----------

25.40	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	6.35	#17-754 €131,00 Qty 6+ €105,00	Contact Us
-------	--------------	---	--------------------------------	-------------------------------	------	--	------------

[#17-755 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

25.40	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	6.35		€131,00 Qty 6+ €105,00	3-4 days
-------	--------------	---	--	-------------------------------	------	--	---------------------------	----------

25.40	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	6.35	#17-757	€147,00 Qty 6+ €117,50	Contact Us
-------	--------------	---	---	--------------------------------	------	-------------------------	---------------------------	------------

[#17-756 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

25.40	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	6.35		€163,00 Qty 6+ €130,50	Contact Us
-------	--------------	---	---	------------------------------	------	--	---------------------------	------------

30.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#17-758	€158,00 Qty 6+ €126,50	3-4 days
-------	--------------	---	--------------------------------	-------------------------------	------	-------------------------	---------------------------	----------

[#17-759 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

30.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00		€158,00 Qty 6+ €126,50	3-4 days
-------	--------------	---	--	-------------------------------	------	--	---------------------------	----------

30.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#17-761	€173,00 Qty 6+ €138,50	3-4 days
-------	--------------	---	---	--------------------------------	------	-------------------------	---------------------------	----------

[#17-760 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

30.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00		€194,00 Qty 6+ €155,00	3-4 days
-------	--------------	---	---	------------------------------	------	--	---------------------------	----------

-	$\lambda/10$	30.0 x 30.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#17-762	€158,00 Qty 6+ €126,50	3-4 days
---	--------------	-------------	--------------------------------	-------------------------------	------	-------------------------	---------------------------	----------

[#17-763 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	$\lambda/10$	30.0 x 30.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00		€158,00 Qty 6+ €126,50	3-4 days
---	--------------	-------------	--	-------------------------------	------	--	---------------------------	----------

-	$\lambda/10$	30.0 x 30.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#17-765	€173,00 Qty 6+ €138,50	Contact Us
---	--------------	-------------	---	--------------------------------	------	-------------------------	---------------------------	------------

[#17-764 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	$\lambda/10$	30.0 x 30.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00		€194,00 Qty 6+ €155,00	3-4 days
---	--------------	-------------	---	------------------------------	------	--	---------------------------	----------

40.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#17-779	€179,00 Qty 6+ €143,00	3-4 days
-------	--------------	---	--------------------------------	-------------------------------	------	-------------------------	---------------------------	----------

40.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#17-780	€179,00 Qty 6+ €143,00	Contact Us
-------	--------------	---	--	-------------------------------	------	-------------------------	---------------------------	------------

40.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#17-781	€236,00 Qty 6+ €189,00	3-4 days
-------	--------------	---	---	------------------------------	------	-------------------------	---------------------------	----------

40.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#17-782	€214,00 Qty 6+ €171,00	3-4 days
-	$\lambda/10$	40.0 x 40.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#17-783	€179,00 Qty 6+ €143,00	3-4 days
-	$\lambda/10$	40.0 x 40.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#17-784	€179,00 Qty 6+ €143,00	In Stock
-	$\lambda/10$	40.0 x 40.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#17-785	€236,00 Qty 6+ €189,00	3-4 days
-	$\lambda/10$	40.0 x 40.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#17-786	€214,00 Qty 6+ €171,00	3-4 days
50.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#39-854	€195,00 Qty 6+ €156,00	In Stock
50.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#24-273	€195,00 Qty 6+ €156,00	Contact Us
50.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#39-916	€233,00 Qty 6+ €186,50	Contact Us
50.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#39-868	€252,00 Qty 6+ €201,50	Contact Us
-	$\lambda/10$	50.0 x 50.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#39-855	€195,00 Qty 6+ €156,00	3-4 days
-	$\lambda/10$	50.0 x 50.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#24-274	€195,00 Qty 6+ €156,00	3-4 days
-	$\lambda/10$	50.0 x 50.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#39-917	€233,00 Qty 6+ €186,50	3-4 days

-	$\lambda/10$	50.0 x 50.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#39-870	€252,00 Qty 6+ €201,50	3-4 days
75.00	$\lambda/10$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	7.50	#17-793	€478,00 Qty 6+ €382,50	3-4 days
75.00	$\lambda/10$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	7.50	#17-794	€478,00 Qty 6+ €382,50	Contact Us
75.00	$\lambda/10$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	7.50	#17-795	€595,00 Qty 6+ €476,00	3-4 days
75.00	$\lambda/10$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	7.50	#17-796	€545,00 Qty 6+ €436,00	In Stock
-	$\lambda/10$	75.0 x 75.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	7.50	#17-797	€478,00 Qty 6+ €382,50	3-4 days
-	$\lambda/10$	75.0 x 75.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	7.50	#17-798	€478,00 Qty 6+ €382,50	3-4 days
-	$\lambda/10$	75.0 x 75.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	7.50	#17-799	€595,00 Qty 6+ €476,00	3-4 days
-	$\lambda/10$	75.0 x 75.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	7.50	#17-800	€545,00 Qty 6+ €436,00	Contact Us
100.00	$\lambda/10$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	10.00	#17-801	€570,00 Qty 6+ €456,00	3-4 days
100.00	$\lambda/10$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	10.00	#17-802	€570,00 Qty 6+ €456,00	3-4 days
100.00	$\lambda/10$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	10.00	#17-803	€825,00 Qty 6+ €660,00	Contact Us

100.00	$\lambda/10$	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	10.00	#17-804	€755,00 Qty 6+ €604,00	Contact Us
-	$\lambda/10$	100.0 x 100.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	10.00	#17-805	€570,00 Qty 6+ €456,00	In Stock
-	$\lambda/10$	100.0 x 100.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	10.00	#17-806	€570,00 Qty 6+ €456,00	3-4 days
 Edmund optics worldwide			R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 700 - 10,000nm	Protected Gold (700- 10000nm)	10.00	#17-807	€825,00 Qty 6+ €660,00	3-4 days
Copyright 2023 Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK Phone: 1-800-363-1992 : www.edmundoptics.com								
-	$\lambda/10$	100.0 x 100.0	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	10.00	#17-808	€755,00 Qty 6+ €604,00	3-4 days