

[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Pinholes and Slits](#)

Acktar Blackened Pinholes See More by [Acktar](#)



- Low Reflectance from the EUV to SWIR
- 99% Absorbance Blackening Coating
- Aperture Sizes from 20 to 1000µm
- Available Unmounted and Mounted

Common Specifications

Physical & Mechanical Properties

Construction:	Stainless Steel
----------------------	-----------------

Material Properties

Absorbance (%):	99
------------------------	----

Technical Information

Products

Type	Outer Diameter (mm)	Construction	Fixed Aperture Diameter (µm)	Stock Number	Price	Buy
Unmounted	9.53	Stainless Steel	20	#15-386	€145,23 Volume Pricing	3 In Stock
Unmounted	9.53	Stainless Steel	25	#15-387	€145,23 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	50	#12-166	€145,23 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	75	#15-388	€145,23 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	100	#12-167	€145,23 Volume Pricing	5 In Stock
Unmounted	9.53	Stainless Steel	150	#15-389	€145,23 Volume Pricing	4 In Stock
Unmounted	9.53	Stainless Steel	200	#12-168	€145,23 Volume Pricing	5 In Stock
Unmounted	9.53	Stainless Steel	300	#15-390	€145,23 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	400	#15-391	€145,23 Volume Pricing	2 In Stock
Unmounted	9.53	Stainless Steel	500	#12-169	€145,23 Volume Pricing	4 In Stock
Unmounted	9.53	Stainless Steel	600	#15-392	€145,23 Volume Pricing	8 In Stock
Unmounted	9.53	Stainless Steel	800	#16-738	€145,23 Volume Pricing	4 In Stock
Unmounted	9.53	Stainless Steel	1000	#12-170	€145,23 Volume Pricing	5 In Stock
Mounted	12.7	Stainless Steel	25	#16-821	€155,53 Volume Pricing	3 In Stock
Mounted	12.7	Stainless Steel	50	#16-822	€155,53 Volume Pricing	20+ In Stock
Mounted	12.7	Stainless Steel	75	#16-823	€155,53 Volume Pricing	20+ In Stock
Mounted	12.7	Stainless Steel	100	#16-824	€155,53 Volume Pricing	2 In Stock

Mounted	12.7	Stainless Steel	150	#16-825	€155,53 Volume Pricing	1 In Stock
Mounted	12.7	Stainless Steel	200	#16-826	€155,53 Volume Pricing	2 In Stock
Mounted	12.7	Stainless Steel	300	#16-827	€155,53 Volume Pricing	4 In Stock
Mounted	12.7	Stainless Steel	500	#16-828	€155,53 Volume Pricing	5 In Stock
Mounted	12.7	Stainless Steel	1000	#16-829	€155,53 Volume Pricing	Contact Us
Mounted	25.0	Stainless Steel	20	#15-393	€155,53 Volume Pricing	4 In Stock
Mounted	25.0	Stainless Steel	25	#15-394	€155,53 Volume Pricing	5 In Stock
Mounted	25.0	Stainless Steel	50	#12-171	€155,53 Volume Pricing	5 In Stock
Mounted	25.0	Stainless Steel	75	#15-395	€155,53 Volume Pricing	3 In Stock
Mounted	25.0	Stainless Steel	100	#12-172	€155,53 Volume Pricing	6 In Stock
Mounted	25.0	Stainless Steel	150	#15-396	€155,53 Volume Pricing	4 In Stock
Mounted	25.0	Stainless Steel	200	#12-173	€155,53 Volume Pricing	5 In Stock
Mounted	25.0	Stainless Steel	300	#15-397	€155,53 Volume Pricing	2 In Stock
Mounted	25.0	Stainless Steel	400	#15-398	€155,53 Volume Pricing	3 In Stock
Mounted	25.0	Stainless Steel	500	#12-174	€155,53 Volume Pricing	2 In Stock
Mounted	25.0	Stainless Steel	600	#15-399	€155,53 Volume Pricing	2 In Stock
Mounted	25.0	Stainless Steel	800	#16-739	€155,53 Volume Pricing	2 In Stock
Mounted	25.0	Stainless Steel	1000	#12-175	€155,53 Volume Pricing	1 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com