

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Focusing \(Concave\) Mirrors](#)

TECHSPEC® Uncoated Concave Laser Mirrors



- High Precision Fused Silica Mirror Substrates
- Large Selection of Diameters and Focal Lengths
- Custom Coating Options Available

Common Specifications

Physical & Mechanical Properties

Clear Aperture (%):	90
---------------------	----

Optical Properties

Substrate:	Fused Silica (Corning 7980)
------------	---

Surface Quality:	20-10
------------------	-------

Coating:	Uncoated
----------	----------

Technical Information

Products

Dia. (mm)	EFL (mm)	Coating	Stock Number	Price	Buy
#27-583 New					
					
New					
12.70	12.50	Uncoated	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€100,94 Volume Pricing	3 In Stock
#27-584 New					
					
New					
12.70	25.00	Uncoated	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€100,94 Volume Pricing	5 In Stock
#27-585 New					
					
New					
12.70	37.50	Uncoated	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€100,94 Volume Pricing	5 In Stock

[#27-586 New](#)



New

12.70 50.00 Uncoated

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

€100,94
[Volume Pricing](#)

5 In Stock

[#27-587 New](#)



New

12.70 75.00 Uncoated

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

€100,94
[Volume Pricing](#)

5 In Stock

[#27-593 New](#)



New

12.70 100.00 Uncoated

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

€100,94
[Volume Pricing](#)

5 In Stock

12.70 125.00 Uncoated

[#27-594](#)

€100,94
[Volume Pricing](#)

5 In Stock

[#27-595 New](#)



New

12.70 250.00 Uncoated

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

€100,94
[Volume Pricing](#)

5 In Stock

[#27-596 New](#)



New

12.70 500.00 Uncoated

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

€100,94
[Volume Pricing](#)

5 In Stock

12.70 750.00 Uncoated

[#27-597](#)

€100,94
[Volume Pricing](#)

1 In Stock

12.70 1,000.00 Uncoated

[#27-598](#)

€100,94
[Volume Pricing](#)

Contact Us

12.70 1,500.00 Uncoated

[#27-599](#)

€100,94
[Volume Pricing](#)

1 In Stock

25.40 25.00 Uncoated

[#39-973](#)

€114,33
[Volume Pricing](#)

20+ In Stock

25.40 50.00 Uncoated

[#39-974](#)

€114,33
[Volume Pricing](#)

16 In Stock

25.40 75.00 Uncoated

[#39-975](#)

€114,33
[Volume Pricing](#)

15 In Stock

[#27-573 New](#)



New

25.40 4.92 Uncoated

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

€124,63
[Volume Pricing](#)

5 In Stock

25.40 100.00 Uncoated

[#39-977](#)

€114,33
[Volume Pricing](#)

20+ In Stock

[#27-575 New](#)



New

25.40 5.35 Uncoated

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

€124,63
[Volume Pricing](#)

5 In Stock

25.40 200.00 Uncoated

[#39-978](#)

€114,33
[Volume Pricing](#)

20+ In Stock

25.40 125.00 Uncoated

[#27-576](#)

€124,63
[Volume Pricing](#)

1 In Stock

25.40 500.00 Uncoated

[#39-979](#)

€114,33
[Volume Pricing](#)

20+ In Stock

[#27-577 New](#)



New

25.40 5.84 Uncoated

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

€124,63
[Volume Pricing](#)

1 In Stock

25.40	375.00	Uncoated	#27-578	€124,63 Volume Pricing	5 In Stock
25.40	750.00	Uncoated	#27-579	€124,63 Volume Pricing	5 In Stock
25.40	1,000.00	Uncoated	#27-580	€124,63 Volume Pricing	16 In Stock
25.40	1,250.00	Uncoated	#27-581	€124,63 Volume Pricing	4 In Stock
25.40	1,500.00	Uncoated	#27-582	€124,63 Volume Pricing	20+ In Stock
50.80	50.00	Uncoated	#11-347	€212,18 Volume Pricing	20+ In Stock
50.80	100.00	Uncoated	#11-348	€211,15 Volume Pricing	13 In Stock
50.80	150.00	Uncoated	#11-349	€212,18 Volume Pricing	20+ In Stock
50.80	250.00	Uncoated	#11-350	€212,18 Volume Pricing	20+ In Stock
50.80	500.00	Uncoated	#11-352	€212,18 Volume Pricing	20+ In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com