

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Laser Mirrors](#)

TECHSPEC® Nd:YAG Laser Line Mirrors



- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

Common Specifications

Optical Properties

Surface Quality:	10-5	Surface Flatness (P-V):	$\lambda/10$
Coating Type:	Dielectric	Substrate:	Fused Silica (Corning 7980)

Technical Information

Products

Wavelength Range (nm)	DWL (nm)	Dia. (mm)	Dimensions (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
263 - 268	266	6.35	-	4.00	45	#38-829	€115,36 Volume Pricing	14 In Stock
263 - 268	266	12.50	-	6.00	45	#47-980	€126,69 Volume Pricing	3 In Stock
263 - 268	266	12.70	-	6.35	45	#34-813	€126,69 Volume Pricing	Contact Us
263 - 268	266	19.10	-	6.35	45	#34-814	€136,99 Volume Pricing	4 In Stock
263 - 268	266	25.00	-	6.00	45	#47-981	€147,29 Volume Pricing	7 In Stock
263 - 268	266	25.40	-	6.35	45	#34-815	€147,29 Volume Pricing	2 In Stock
263 - 268	266	38.10	-	6.35	45	#34-816	€174,07 Volume Pricing	Contact Us
263 - 268	266	50.00	-	10.00	45	#63-116	€267,80 Volume Pricing	12 In Stock
263 - 268	266	50.80	-	9.53	45	#38-831	€267,80 Volume Pricing	5 In Stock
263 - 268	266	-	12.7 x 12.7	6.35	45	#39-581	€144,20 Volume Pricing	3 In Stock
263 - 268	266	-	19.1 x 12.7	6.35	45	#39-582	€151,41 Volume Pricing	8 In Stock
263 - 268	266	-	25.4 x 25.4	6.35	45	#39-583	€168,92 Volume Pricing	11 In Stock
263 - 268	266	-	38.1 x 25.4	6.35	45	#39-585	€174,07 Volume Pricing	1 In Stock
263 - 268	266	-	6.35 x 6.35	3.18	45	#39-576	€132,87 Volume Pricing	13 In Stock

[#39-579 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

263 - 268	266	-	9.53 x 6.35	3.18	45		€89,56	6 In Stock
-----------	-----	---	-------------	------	----	--	--------	------------

[#63-110 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

255 - 275	266	12.50	-	6.00	0		€49,39	9 In Stock
-----------	-----	-------	---	------	---	--	--------	------------

263 - 268	266	4.00	-	3.00	0-45	#12-623	€119,48 Volume Pricing	14 In Stock
-----------	-----	------	---	------	------	-------------------------	---	-------------

263 - 268	266	6.35	-	4.00	0-45	#38-832	€139,05 Volume Pricing	20+ In Stock
-----------	-----	------	---	------	------	-------------------------	---	--------------

-	266	12.50	-	6.00	0-45	#88-523	€151,41 Volume Pricing	Contact Us
---	-----	-------	---	------	------	-------------------------	---	------------

263 - 268	266	12.70	-	6.35	0-45	#38-833	€151,41 Volume Pricing	3 In Stock
-----------	-----	-------	---	------	------	-------------------------	---	------------

263 - 268	266	19.10	-	6.35	0-45	#38-834	€163,77 Volume Pricing	20+ In Stock
-	266	25.00	-	6.00	0-45	#88-524	€174,07 Volume Pricing	20+ In Stock
263 - 268	266	25.40	-	6.35	0-45	#38-835	€174,07 Volume Pricing	20+ In Stock
263 - 268	266	38.10	-	6.35	0-45	#38-838	€203,94 Volume Pricing	2 In Stock
-	266	50.00	-	10.00	0-45	#88-525	€306,94 Volume Pricing	5 In Stock
263 - 268	266	50.80	-	9.53	0-45	#38-841	€306,94 Volume Pricing	8 In Stock
-	266	76.20	-	12.70	0-45	#20-418	€759,11 Volume Pricing	Contact Us
-	266	-	12.7 x 12.7	6.35	0-45	#39-589	€157,59 Volume Pricing	12 In Stock
-	266	-	19.1 x 12.7	6.35	0-45	#39-590	€163,77 Volume Pricing	12 In Stock
-	266	-	25.4 x 25.4	6.35	0-45	#39-591	€180,25 Volume Pricing	3 In Stock
-	266	-	38.1 x 25.4	6.35	0-45	#39-592	€187,46 Volume Pricing	1 In Stock
-	266	-	6.35 x 6.35	3.18	0-45	#39-586	€144,20 Volume Pricing	14 In Stock

[#39-587 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

-	266	-	9.53 x 6.35	3.18	0-45		€97,80	3 In Stock
351 - 358	355	6.35	-	4.00	45	#38-858	€115,36 Volume Pricing	7 In Stock

351 - 358	355	12.50	-	6.00	45	#47-323	€126,69 Volume Pricing	Contact Us
351 - 358	355	12.70	-	6.35	45	#34-818	€126,69 Volume Pricing	2 In Stock
351 - 358	355	19.10	-	6.35	45	#34-819	€136,99 Volume Pricing	20+ In Stock
351 - 358	355	25.00	-	6.00	45	#47-324	€147,29 Volume Pricing	20+ In Stock
351 - 358	355	25.40	-	6.35	45	#34-820	€147,29 Volume Pricing	20+ In Stock
351 - 358	355	38.10	-	6.35	45	#34-821	€174,07 Volume Pricing	8 In Stock
351 - 358	355	50.00	-	10.00	45	#63-117	€267,80 Volume Pricing	10 In Stock
351 - 358	355	50.80	-	9.53	45	#38-862	€267,80 Volume Pricing	20+ In Stock
351 - 358	355	-	12.7 x 12.7	6.35	45	#39-616	€144,20 Volume Pricing	12 In Stock
351 - 358	355	-	19.1 x 12.7	6.35	45	#39-617	€151,41 Volume Pricing	20+ In Stock
351 - 358	355	-	25.4 x 25.4	6.35	45	#39-618	€168,92 Volume Pricing	4 In Stock
351 - 358	355	-	38.1 x 25.4	6.35	45	#39-619	€174,07 Volume Pricing	5 In Stock
351 - 358	355	-	6.35 x 6.35	3.18	45	#39-611	€132,87 Volume Pricing	7 In Stock

[#39-615 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

351 - 358	355	-	9.53 x 6.35	3.18	45		€89,56	1 In Stock
-----------	-----	---	-------------	------	----	--	--------	------------

351 - 358	355	4.00	-	3.00	0-45	#12-625	€119,48 Volume Pricing	15 In Stock
351 - 358	355	6.35	-	4.00	0-45	#38-863	€139,05 Volume Pricing	20+ In Stock
-	355	12.50	-	6.00	0-45	#88-526	€151,41 Volume Pricing	20+ In Stock
351 - 358	355	12.70	-	6.35	0-45	#38-864	€151,41 Volume Pricing	20+ In Stock
351 - 358	355	19.10	-	6.35	0-45	#38-865	€163,77 Volume Pricing	20+ In Stock
-	355	25.00	-	6.00	0-45	#88-527	€174,07 Volume Pricing	1 In Stock
351 - 358	355	25.40	-	6.35	0-45	#38-866	€174,07 Volume Pricing	20+ In Stock
351 - 358	355	38.10	-	6.35	0-45	#38-868	€203,94 Volume Pricing	9 In Stock
-	355	50.00	-	10.00	0-45	#88-528	€306,94 Volume Pricing	4 In Stock
351 - 358	355	50.80	-	9.53	0-45	#38-870	€306,94 Volume Pricing	5 In Stock
-	355	76.20	-	12.70	0-45	#20-420	€759,11 Volume Pricing	9 In Stock
-	355	-	12.7 x 12.7	6.35	0-45	#39-622	€157,59 Volume Pricing	5 In Stock
-	355	-	19.1 x 12.7	6.35	0-45	#39-623	€163,77 Volume Pricing	6 In Stock
-	355	-	25.4 x 25.4	6.35	0-45	#39-624	€180,25 Volume Pricing	1 In Stock
-	355	-	38.1 x 25.4	6.35	0-45	#39-625	€187,46 Volume Pricing	5 In Stock
-	355	-	6.35 x 6.35	3.18	0-45	#39-620	€144,20 Volume Pricing	5 In Stock

[#39-621 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

- 355 - 9.53 x 6.35 3.18 0-45 €97,80 10 In Stock

523 - 537	532	6.35	-	4.00	45	#38-887	€115,36 Volume Pricing	3 In Stock
523 - 537	532	12.50	-	6.00	45	#45-990	€126,69 Volume Pricing	20+ In Stock
523 - 537	532	12.70	-	6.35	45	#34-823	€126,69 Volume Pricing	20+ In Stock
523 - 537	532	19.10	-	6.35	45	#34-824	€136,99 Volume Pricing	17 In Stock
523 - 537	532	25.00	-	6.00	45	#45-991	€147,29 Volume Pricing	20+ In Stock
523 - 533	532	25.40	-	6.35	45	#34-825	€147,29 Volume Pricing	20+ In Stock
523 - 537	532	38.10	-	6.35	45	#34-826	€174,07 Volume Pricing	5 In Stock
523 - 537	532	50.00	-	10.00	45	#47-157	€267,80 Volume Pricing	20+ In Stock
523 - 537	532	50.80	-	9.53	45	#38-889	€267,80 Volume Pricing	20+ In Stock
-	532	76.20	-	12.70	0-45	#20-422	€759,11 Volume Pricing	5 In Stock
523 - 537	532	-	12.7 x 12.7	6.35	45	#39-641	€144,20 Volume Pricing	4 In Stock
523 - 537	532	-	19.1 x 12.7	6.35	45	#39-642	€151,41 Volume Pricing	20+ In Stock
523 - 537	532	-	25.4 x 25.4	6.35	45	#39-643	€168,92 Volume Pricing	3 In Stock

523 - 537	532	-	38.1 x 25.4	6.35	45	#39-644	€174,07 Volume Pricing	5 In Stock
523 - 537	532	-	6.35 x 6.35	3.18	45	#39-639	€132,87 Volume Pricing	9 In Stock
#39-640 Clearance								
 Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.								
523 - 537	532	-	9.53 x 6.35	3.18	45		€89,56	2 In Stock
523 - 537	532	4.00	-	3.00	0-45	#12-627	€119,48 Volume Pricing	Contact Us
523 - 537	532	6.35	-	4.00	0-45	#38-890	€139,05 Volume Pricing	9 In Stock
-	532	12.50	-	6.00	0-45	#88-529	€151,41 Volume Pricing	20+ In Stock
523 - 537	532	12.70	-	6.35	0-45	#38-891	€151,41 Volume Pricing	20+ In Stock
523 - 537	532	19.10	-	6.35	0-45	#38-892	€163,77 Volume Pricing	14 In Stock
-	532	25.00	-	6.00	0-45	#88-530	€174,07 Volume Pricing	4 In Stock
523 - 537	532	25.40	-	6.35	0-45	#38-893	€174,07 Volume Pricing	20+ In Stock
523 - 537	532	38.10	-	6.35	0-45	#38-895	€203,94 Volume Pricing	3 In Stock
-	532	50.00	-	10.00	0-45	#88-531	€306,94 Volume Pricing	4 In Stock
523 - 537	532	50.80	-	9.53	0-45	#38-897	€306,94 Volume Pricing	20+ In Stock
-	532	-	12.7 x 12.7	6.35	0-45	#39-647	€157,59 Volume Pricing	7 In Stock

-	532	-	19.1 x 12.7	6.35	0-45	#39-648	€163,77 Volume Pricing	5 In Stock
-	532	-	25.4 x 25.4	6.35	0-45	#39-649	€180,25 Volume Pricing	13 In Stock
-	532	-	38.1 x 25.4	6.35	0-45	#39-650	€187,46 Volume Pricing	10 In Stock
-	532	-	6.35 x 6.35	3.18	0-45	#39-645	€144,20 Volume Pricing	20+ In Stock

[#39-646 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

-	532, 1064	50.00	-	10.00	45	#63-118	€261,62 Volume Pricing	15 In Stock
1046 - 1074	1064	19.05	-	9.53	0	#17-624	€136,99 Volume Pricing	1 In Stock
1046 - 1074	1064	6.35	-	4.00	45	#38-898	€115,36 Volume Pricing	7 In Stock
1046 - 1074	1064	12.50	-	6.00	45	#45-986	€126,69 Volume Pricing	20+ In Stock
1046 - 1074	1064	12.70	-	6.35	45	#34-828	€126,69 Volume Pricing	Contact Us
1046 - 1074	1064	19.10	-	6.35	45	#34-829	€136,99 Volume Pricing	3 In Stock
1046 - 1074	1064	25.00	-	6.00	45	#45-987	€147,29 Volume Pricing	20+ In Stock
1046 - 1074	1064	25.40	-	6.35	45	#34-830	€147,29 Volume Pricing	20+ In Stock
1046 - 1074	1064	38.10	-	6.35	45	#34-831	€174,07 Volume Pricing	20+ In Stock

1046 - 1074	1064	50.00	-	10.00	45	#47-156	€267,80 Volume Pricing	20+ In Stock
1046 - 1074	1064	50.80	-	9.53	45	#38-900	€267,80 Volume Pricing	20+ In Stock
-	1064	76.20	-	12.70	0-45	#20-430	€759,11 Volume Pricing	20+ In Stock
1046 - 1074	1064	-	12.7 x 12.7	6.35	45	#39-653	€144,20 Volume Pricing	6 In Stock
1046 - 1074	1064	-	19.1 x 12.7	6.35	45	#39-654	€151,41 Volume Pricing	1 In Stock
1046 - 1074	1064	-	25.4 x 25.4	6.35	45	#39-655	€168,92 Volume Pricing	13 In Stock
1046 - 1074	1064	-	38.1 x 25.4	6.35	45	#39-656	€174,07 Volume Pricing	6 In Stock
1046 - 1074	1064	-	6.35 x 6.35	3.18	45	#39-651	€132,87 Volume Pricing	5 In Stock
1046 - 1074	1064	4.00	-	3.00	0-45	#12-629	€119,48 Volume Pricing	5 In Stock
1046 - 1074	1064	6.35	-	4.00	0-45	#38-901	€139,05 Volume Pricing	8 In Stock
-	1064	12.50	-	6.00	0-45	#88-532	€151,41 Volume Pricing	20+ In Stock
1046 - 1074	1064	12.70	-	6.35	0-45	#38-902	€151,41 Volume Pricing	Contact Us
1046 - 1074	1064	19.10	-	6.35	0-45	#38-904	€163,77 Volume Pricing	10 In Stock
-	1064	25.00	-	6.00	0-45	#88-533	€174,07 Volume Pricing	20+ In Stock
1046 - 1074	1064	25.40	-	3.18	0-45	#14-340	€174,07 Volume Pricing	Contact Us
1046 - 1074	1064	25.40	-	6.35	0-45	#38-905	€174,07 Volume Pricing	20+ In Stock
1046 - 1074	1064	38.10	-	6.35	0-45	#38-907	€203,94 Volume Pricing	11 In Stock
-	1064	50.00	-	10.00	0-45	#88-534	€306,94 Volume Pricing	7 In Stock
1046 - 1074	1064	50.80	-	9.53	0-45	#38-909	€306,94 Volume Pricing	20+ In Stock
-	1064	-	12.7 x 12.7	6.35	0-45	#39-659	€157,59 Volume Pricing	20+ In Stock
-	1064	-	19.1 x 12.7	6.35	0-45	#39-660	€163,77 Volume Pricing	5 In Stock

-	1064	-	25.4 x 25.4	6.35	0-45	#39-661	€180,25 Volume Pricing	8 In Stock
-	1064	-	38.1 x 25.4	6.35	0-45	#39-662	€187,46 Volume Pricing	20+ In Stock
-	1064	-	6.35 x 6.35	3.18	0-45	#39-657	€144,20 Volume Pricing	20+ In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
 Phone: 1-800-363-1992 :
www.edmundoptics.com