

[All Products](#) / [Optics](#) / [Ultrafast Optics](#) / [Ultrafast Lenses and Windows](#)
TECHSPEC® Ultrafast Thin Windows


- 1mm Thickness for Limited GDD
- Low Loss Broadband IBS Anti-Reflection Coating
- Designs for Wavelengths from 370nm to 2200nm
- Coating GDD of $\pm 30\text{fs}^2$
- UV or IR Grade Fused Silica Substrates

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Clear Aperture (%):	90
Thickness (mm):	1.00 $\pm$ 0.10	Edges:	Fine Ground
Knoop Hardness (kg/mm²):	522.00	Parallelism (arcsec):	≤ 30
Poisson's Ratio:	0.16	Young's Modulus (GPa):	73

Optical Properties


Abbe Number (v_d):	67.8	Index of Refraction (n_d):	1.458
Surface Quality:	20-10	Transmitted Wavefront, P-V:	$\lambda/6$

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):	0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)	Density (g/cm³):	2.20
---	---	------------------------------------	------

Technical Information

Calculated GVD of Fused Silica



Products

Dia. (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
12.70	1.00	BBAR (370-550nm)	#11-746	€143,00 Volume Pricing	Contact Us
25.40	1.00	BBAR (370-550nm)	#11-747	€202,00 Volume Pricing	4 In Stock
50.80	1.00	BBAR (370-550nm)	#11-748	€315,00 Volume Pricing	20+ In Stock
12.70	1.00	BBAR (700-900nm)	#11-743	€143,00 Volume Pricing	20+ In Stock
25.40	1.00	BBAR (700-900nm)	#11-744	€202,00 Volume Pricing	15 In Stock
50.80	1.00	BBAR (700-900nm)	#11-745	€315,00 Volume Pricing	14 In Stock
12.70	1.00	BBAR (950-1150nm)	#11-740	€143,00 Volume Pricing	20+ In Stock
25.40	1.00	BBAR (950-1150nm)	#11-741	€202,00 Volume Pricing	20+ In Stock
50.80	1.00	BBAR (950-1150nm)	#11-742	€315,00 Volume Pricing	11 In Stock
12.70	1.00	BBAR (1900-2200nm)	#11-737	€152,00 Volume Pricing	14 In Stock
25.40	1.00	BBAR (1900-2200nm)	#11-738	€216,00 Volume Pricing	16 In Stock
50.80	1.00	BBAR (1900-2200nm)	#11-739	€329,00 Volume Pricing	12 In Stock
12.70	1.00	Uncoated	#11-749	€106,00 Volume Pricing	Contact Us
25.40	1.00	Uncoated	#11-750	€126,00 Volume Pricing	20+ In Stock
50.80	1.00	Uncoated	#11-751	€219,00 Volume Pricing	20+ In Stock
12.70	1.00	Uncoated	#11-752	€115,00 Volume Pricing	20+ In Stock

25.40	1.00	Uncoated	#11-753	€135,00 Volume Pricing	10 In Stock
50.80	1.00	Uncoated	#11-754	€242,00 Volume Pricing	20+ In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
Phone: 1-800-363-1992 :
www.edmundoptics.com