

[All Products](#) / [Lasers](#) / [Laser Mechanics](#)

Acktar Blackened Laser Beam Traps and Blocks See More by [Acktar](#)



- Coated for High Absorbance of Laser Light
- Tubular Beam Trap or Thin, Flat Beam Block Designs
- M6 Tapped Hole for Easy Post Mounting

Common Specifications

Physical & Mechanical Properties

Construction:	Black Anodized Aluminum
---------------	-------------------------

Optical Properties

Wavelength Range (nm):	100 - 10000
------------------------	-------------

Electrical

Maximum Incident Power Density (W/cm ²):	20
--	----

Threading & Mounting

Mounting Threads:	M6 x 1.0
-------------------	----------

Technical Information

Products

Title	Stock Number	Price	Buy
30mm Aperture, Acktar Blackened Laser Beam Trap	#13-515	€251,00 Qty 3+ €236,30	In Stock
51mm Aperture, Acktar Blackened Laser Beam Trap	#13-516	€329,00 Qty 3+ €309,70	3-4 days
92 x 81mm Aperture, Acktar Blackened Laser Beam Block	#13-517	€329,00 Qty 3+ €309,70	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com