

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® HP Series Fixed Focal Length Lenses



- 1.1", C-Mount Lens
- Up to 20 MegaPixels, 1.85µm Pixel Size Sensors
- High Performance (HP), C-Mount Lens for Machine Vision
- 6.5mm to 50mm Focal Length


Common Specifications

Physical & Mechanical Properties

Iris Option:

Variable

Technical Information



Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
#86-568 New  New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!							
6.50	1.1"	f/2.0 - f/16	100 - ∞	C-Mount		€1.295,00	Contact Us
8.00	1.1"	f/1.8 - f/16	100 - ∞	C-Mount	#86-569	€950,00	20+ In Stock
12.00	1.1"	f/1.8 - f/16	100 - ∞	C-Mount	#86-570	€725,00	5 In Stock
16.00	1.1"	f/1.8 - f/16	100 - ∞	C-Mount	#86-571	€725,00	2 In Stock
25.00	1.1"	f/1.8 - f/22	150 - ∞	C-Mount	#86-572	€575,00	20+ In Stock
35.00	1.1"	f/1.8 - f/16	200 - ∞	C-Mount	#86-573	€575,00	20+ In Stock
50.00	4/3"	f/1.8 - f/16	200 - ∞	C-Mount	#86-574	€675,00	11 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com