

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Bar Lights](#)

Advanced Illumination MicroBrite Ultra High Intensity Bar Lights

See More by [Advanced Illumination](#)



- High Intensity Output up to 73,000 Lux
- Compact Housing with T-Slot Mount
- Full Range of Wavelengths Available
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended

Common Specifications

General				
LED Lifetime (hours):		50,000	Type of Illumination:	LED Illuminator
Note:		Optional Manual Intensity Adjustment #86-887 and #89-555 are Available	Manufacturer:	Advanced Illumination
Geometry:		Bar Light	Illumination Mode:	Constant
Physical & Mechanical Properties				
Dimensions (mm):		165.6 x 20.1 x 20.1	Weight (g):	68.9
Hardware & Interface Connectivity				
Connector:		Flying Leads	Input Voltage (V):	24V
Power Supply:		Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855		
Environmental & Durability Factors				
Operating Temperature (°C):			0 - 60	
Environmental Rating:			IP50	

Technical Information

Products

Dimensions (mm)	Color	Wavelength (nm)	Stock Number	Price	Buy
165.6 x 20.1 x 20.1	White	-	#18-540	€615,00	3 In Stock
165.6 x 20.1 x 20.1	UV	365.00	#18-544	€1.485,00	3 In Stock
165.6 x 20.1 x 20.1	Blue	470.00	#18-542	€615,00	1 In Stock
165.6 x 20.1 x 20.1	Green	530.00	#18-543	€615,00	1 In Stock
165.6 x 20.1 x 20.1	Red	625.00	#18-541	€615,00	3 In Stock
165.6 x 20.1 x 20.1	IR	850.00	#18-545	€615,00	3 In Stock
165.6 x 20.1 x 20.1	IR	940.00	#18-546	€615,00	1 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com