

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Bar Lights](#)

Advanced Illumination UltraSeal Washdown Bar Lights See

More by [Advanced Illumination](#)



- IP69K Certified for Extreme Washdown Environments
- Proprietary Housing to Prevent Corrosion and Overheating
- High Intensity Output up to 70,200 Lux
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended

Common Specifications

General	
LED Lifetime (hours):	50000
Type of Illumination:	LED Illuminator
Note:	Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer:	Advanced Illumination
Geometry:	Bar Light
Illumination Mode:	Constant
Hardware & Interface Connectivity	
Connector:	Flying Leads
Input Voltage (V):	24V
Power Supply:	Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Environmental & Durability Factors	
Operating Temperature (°C):	0 - 60
Environmental Rating:	IP69K

Technical Information

Products

Dimensions (mm)	Color	Wavelength (nm)	Stock Number	Price	Buy
171.4 x 42.9 x 24	White	-	#18-623	€848,00	3-4 days
171.4 x 42.9 x 24	Blue	470.00	#18-625	€848,00	3-4 days
171.4 x 42.9 x 24	Green	530.00	#18-626	€848,00	3-4 days
171.4 x 42.9 x 24	Red	625.00	#18-624	€848,00	3-4 days
171.4 x 42.9 x 24	IR	850.00	#18-627	€848,00	3-4 days
171.4 x 42.9 x 24	IR	940.00	#18-628	€848,00	3-4 days
323.8 x 42.9 x 24	White	-	#18-629	€1.380,00	3-4 days
323.8 x 42.9 x 24	Blue	470.00	#18-631	€1.380,00	3-4 days
323.8 x 42.9 x 24	Green	530.00	#18-632	€1.380,00	3-4 days
323.8 x 42.9 x 24	Red	625.00	#18-630	€1.380,00	3-4 days
323.8 x 42.9 x 24	IR	850.00	#18-633	€1.380,00	3-4 days
323.8 x 42.9 x 24	IR	940.00	#18-634	€1.380,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com