

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#)

IDS Imaging uEye+ FA IP65/67 PoE Cameras See More by [IDS Imaging Development Systems](#)



- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

Common Specifications

General

Camera Family: uEye+ FA

Physical & Mechanical Properties

Housing: Full

Sensor

Type of Sensor: Progressive Scan CMOS

Machine Vision Standard: GigE Vision

Hardware & Interface Connectivity

Video Output: GigE (PoE)

Power Supply: Power over Ethernet (PoE) or 12 - 24VDC via GPIO with [#19-692](#)

Threading & Mounting

Mount: C-Mount

Environmental & Durability Factors

Operating Temperature (°C): 0 to +55

Storage Temperature (°C): -20 to +60

Technical Information

Products

Type	Model Number	Camera Sensor Format	Resolution (MegaPixels)	Connector	Mount	Stock Number	Price	Buy
Color	GV-5240FA-C-HQ	1/1.8"	1.31	GigE M12, screwable	C-Mount	#26-295	€725,00	3-4 days
Mono	GV-5240FA-M-GL	1/1.8"	1.31	GigE M12, screwable	C-Mount	#26-296	€725,00	3-4 days
Mono NIR	GV-5240FA-NIR-GL	1/1.8"	1.31	GigE M12, screwable	C-Mount	#26-297	€830,00	3-4 days
Color	GV-5250FA-C-HQ	1/1.8"	1.92	GigE M12, screwable	C-Mount	#26-298	€805,00	3-4 days
Mono	GV-5250FA-M-GL	1/1.8"	1.92	GigE M12, screwable	C-Mount	#26-299	€805,00	3-4 days
Color	GV-5880FA-C-HQ	1/1.8"	6.41	GigE M12, screwable	C-Mount	#26-313	€670,00	3-4 days
Mono	GV-5880FA-M-GL	1/1.8"	6.41	GigE M12, screwable	C-Mount	#26-314	€670,00	3-4 days
Color	GV-5800FA-C-HQ	1"	20.44	GigE M12, screwable	C-Mount	#26-309	€930,00	3-4 days
Mono	GV-5800FA-M-GL	1"	20.44	GigE M12, screwable	C-Mount	#26-310	€930,00	3-4 days
Color	GV-5890FA-C-HQ	1/1.7"	12.00	GigE M12, screwable	C-Mount	#26-315	€725,00	3-4 days
Mono	GV-5890FA-M-GL	1/1.7"	12.00	GigE M12, screwable	C-Mount	#26-316	€725,00	3-4 days
Color	GV-5040FA-C-HQ	1/2.9"	1.58	GigE M12, screwable	C-Mount	#26-287	€675,00	3-4 days
Mono	GV-5040FA-M-GL	1/2.9"	1.58	GigE M12, screwable	C-Mount	#26-288	€675,00	3-4 days
Mono	GV-5260FA-M-GL	1/1.2"	2.30	GigE M12, screwable	C-Mount	#26-300	€810,00	3-4 days

Mono POL	GV- 5080FA- P-GL	2/3"	5.01	GigE M12, screwable	C- Mount	#26-289	€2.810,00	3-4 days
Mono POL	GV- 5000FA- P-GL	1.1"	12.29	GigE M12, screwable	C- Mount	#26-286	€3.740,00	3-4 days
Color	GV- 5280FA- C-HQ	2/3"	5.01	GigE M12, screwable	C- Mount	#26-303	€1.090,00	3-4 days
Mono	GV- 5280FA- M-GL	2/3"	5.01	GigE M12, screwable	C- Mount	#26-304	€1.090,00	Contact Us
Color	GV- 5270FA- C-HQ	1/1.8"	3.19	GigE M12, screwable	C- Mount	#26-301	€610,00	Contact Us
Mono	GV- 5270FA- M-GL	1/1.8"	3.19	GigE M12, screwable	C- Mount	#26-302	€610,00	3-4 days
Color	GV- 5290FA- C-HQ	1"	8.85	GigE M12, screwable	C- Mount	#26-305	€1.755,00	3-4 days
Mono	GV- 5290FA- M-GL	1"	8.85	GigE M12, screwable	C- Mount	#26-306	€1.755,00	3-4 days
Color	GV- 5860FA- C-HQ	1/3"	2.12	GigE M12, screwable	C- Mount	#26-311	€715,00	3-4 days
Mono	GV- 5860FA- M-GL	1/3"	2.12	GigE M12, screwable	C- Mount	#26-312	€715,00	3-4 days
Color	GV- 5200FA- C-HQ	1.1"	12.29	GigE M12, screwable	C- Mount	#26-293	€2.165,00	3-4 days
Mono	GV- 5200FA- M-GL	1.1"	12.29	GigE M12, screwable	C- Mount	#26-294	€2.165,00	3-4 days
Color	GV- 50C0FA- C-HQ	1/2.3"	2.35	GigE M12, screwable	C- Mount	#26-291	€680,00	3-4 days
Mono	GV- 50C0FA- M-GL	1/2.3"	2.35	GigE M12, screwable	C- Mount	#26-292	€680,00	3-4 days
Color	GV- 5990FA- C-HQ	1.1"	20.36	GigE M12, screwable	C- Mount	#26-317	€2.245,00	3-4 days
Mono	GV- 5990FA- M-GL	1.1"	20.36	GigE M12, screwable	C- Mount	#26-318	€2.245,00	3-4 days

[#26-308 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

Color Camera	GV-5580FA-C-HQ Rev.1.2	1/2.5"	4.92	GigE, RJ45 with Screw Locks	C-Mount	€620,00	3-4 days
--------------	------------------------	--------	------	-----------------------------	---------	---------	----------

