

[All Products](#) /
 [Optics](#) /
 [Optical Mirrors](#) /
 [Flat Mirrors](#) /
 [Laser Mirrors](#)

TECHSPEC® Dual Band Laser Line Mirrors



- >99% Reflectivity at Design Wavelengths
- 10-5 Surface Quality for Sensitive Laser Applications
- 532/1064nm, 635-670/1064nm, or 800/1030nm Wavelength Bands
- [TECHSPEC® Nd:YAG Laser Line Mirrors](#) Also Available

Common Specifications

Physical & Mechanical Properties

Clear Aperture (%):	>90
---------------------	-----

Optical Properties

Surface Quality:	10-5
------------------	------

Surface Flatness (P-V):	$\lambda/10$
-------------------------	--------------

Coating Type:	Dielectric
---------------	------------

Substrate:	Fused Silica (Corning 7980)
------------	---

Technical Information

Products

DWL (nm)	Dia. (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
532, 1064	12.50	3.00	45	#20-371	€146,00 Qty 6+ €128,00	3-4 days
532, 1064	12.50	6.00	45	#47-976	€146,00 Qty 6+ €128,00	3-4 days
532, 1064	12.70	6.35	45	#28-974	€174,00 Qty 6+ €153,00	3-4 days
532, 1064	25.00	3.00	45	#20-216	€167,00 Qty 6+ €147,00	3-4 days
532, 1064	25.00	6.00	45	#47-977	€167,00 Qty 6+ €147,00	In Stock
532, 1064	25.40	6.35	45	#28-975	€199,00 Qty 6+ €175,00	3-4 days
532, 1064	50.00	10.00	45	#63-118	€254,00 Qty 6+ €228,00	3-4 days
532, 1064	50.80	9.53	45	#28-976	€338,00 Qty 6+ €298,00	Contact Us
532, 1064	76.20	12.70	45	#27-037	€725,00 Qty 6+ €650,00	Contact Us
532, 1064	50.80	6.35	45	#20-612	€284,00 Qty 6+ €252,00	3-4 days
532, 635, 650, 1064	12.70	6.35	45	#26-926	€164,00 Qty 6+ €155,00	3-4 days
532, 635, 650, 1064	12.70	6.35	0 - 45	#28-980	€195,00 Qty 6+ €171,00	3-4 days
532, 635, 650, 1064	25.40	6.35	45	#26-927	€186,00 Qty 6+ €177,00	3-4 days
532, 635, 650, 1064	25.40	6.35	0 - 45	#28-981	€223,00 Qty 6+ €196,00	3-4 days
532, 635, 650, 1064	50.80	9.53	45	#26-928	€318,00 Qty 6+ €302,00	Contact Us
532, 635, 650, 1064	50.80	9.53	0 - 45	#28-982	€379,00 Qty 6+ €333,00	3-4 days

635, 670, 1064	12.50	3.00	45	#20-399	€146,00 Qty 6+ €128,00	3-4 days
635, 670, 1064	12.50	6.00	45	#47-978	€146,00 Qty 6+ €128,00	Contact Us
635, 670, 1064	12.70	6.35	45	#28-977	€174,00 Qty 6+ €153,00	3-4 days
635, 670, 1064	25.00	3.00	45	#20-599	€167,00 Qty 6+ €147,00	3-4 days
635, 670, 1064	25.00	6.00	45	#47-979	€167,00 Qty 6+ €147,00	3-4 days
635, 670, 1064	25.40	6.35	45	#28-978	€199,00 Qty 6+ €175,00	3-4 days
635, 670, 1064	50.00	10.00	45	#63-119	€284,00 Qty 6+ €252,00	Contact Us
635, 670, 1064	50.80	6.35	45	#20-607	€284,00 Qty 6+ €252,00	3-4 days
635, 670, 1064	50.80	9.53	45	#28-979	€338,00 Qty 6+ €298,00	3-4 days
635, 670, 1064	76.20	12.70	45	#27-038	€725,00 Qty 6+ €650,00	3-4 days
800, 1030	12.70	6.35	45	#28-965	€174,00 Qty 6+ €153,00	3-4 days
800, 1030	12.70	6.35	0 - 45	#28-968	€209,00 Qty 6+ €189,00	3-4 days
800, 1030	25.40	6.35	45	#28-966	€199,00 Qty 6+ €175,00	3-4 days
800, 1030	25.40	6.35	0 - 45	#28-969	€240,00 Qty 6+ €215,00	3-4 days
800, 1030	50.80	9.53	45	#28-967	€338,00 Qty 6+ €298,00	3-4 days
800, 1030	50.80	9.53	0 - 45	#28-970	€399,00 Qty 6+ €359,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com