

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Machine Vision Filters](#) / [Neutral Density \(ND\) Filters](#)

Machine Vision Absorptive Neutral Density (ND) Filters



- Multiple Mounting Sizes and Threads Available
- 40-20 Surface Quality
- Helps Minimize Pixel Saturation

Common Specifications

Optical Properties

Substrate:	ND Filter Glass	Surface Quality:	40-20
Blocking Wavelength Range (nm):	425 - 675		

Technical Information

Products

Filter Thread	Optical Density OD (Average)	Transmission (%)	Stock Number	Price	Buy
M77 x 0.75	0.3	50.00	#21-410	€184,00 Qty 10+ €174,80	3-4 days
M77 x 0.75	0.6	25.00	#21-411	€184,00 Qty 10+ €174,80	3-4 days
M77 x 0.75	0.9	12.50	#21-412	€184,00 Qty 10+ €174,80	3-4 days
M77 x 0.75	1.2	6.25	#21-413	€184,00 Qty 10+ €174,80	3-4 days
M77 x 0.75	2.0	1.00	#21-414	€264,00 Qty 10+ €250,80	3-4 days
M77 x 0.75	3.0	0.10	#21-415	€264,00 Qty 10+ €250,80	3-4 days
M77 x 0.75	4.0	0.01	#21-416	€264,00 Qty 10+ €250,80	3-4 days
M39 x 0.50	0.3	50.00	#21-427	€74,00 Qty 10+ €70,30	3-4 days
M39 x 0.50	0.6	25.00	#21-428	€74,00 Qty 10+ €70,30	3-4 days
M39 x 0.50	0.9	12.50	#21-429	€74,00 Qty 10+ €70,30	3-4 days
M39 x 0.50	1.2	6.25	#21-430	€74,00 Qty 10+ €70,30	3-4 days
M39 x 0.50	2.0	1.00	#21-431	€130,00 Qty 10+ €123,50	3-4 days
M39 x 0.50	3.0	0.10	#21-432	€130,00 Qty 10+ €123,50	3-4 days
M39 x 0.50	4.0	0.01	#21-433	€130,00 Qty 10+ €123,50	3-4 days
M49 x 0.75	0.3	50.00	#21-444	€74,00 Qty 10+ €70,30	3-4 days
M49 x 0.75	0.6	25.00	#21-445	€74,00 Qty 10+ €70,30	3-4 days

M49 x 0.75	0.9	12.50	#21-446	€74,00 Qty 10+ €70,30	3-4 days
M49 x 0.75	1.2	6.25	#21-447	€74,00 Qty 10+ €70,30	In Stock
M49 x 0.75	2.0	1.00	#21-448	€130,00 Qty 10+ €123,50	3-4 days
M49 x 0.75	3.0	0.10	#21-449	€130,00 Qty 10+ €123,50	3-4 days
M49 x 0.75	4.0	0.01	#21-450	€130,00 Qty 10+ €123,50	3-4 days
M67 x 0.75	0.3	50.00	#21-461	€116,00 Qty 10+ €110,20	3-4 days
M67 x 0.75	0.6	25.00	#21-462	€116,00 Qty 10+ €110,20	3-4 days
M67 x 0.75	0.9	12.50	#21-463	€116,00 Qty 10+ €110,20	3-4 days
M67 x 0.75	1.2	6.25	#21-464	€116,00 Qty 10+ €110,20	3-4 days
M67 x 0.75	2.0	1.00	#21-465	€170,00 Qty 10+ €161,50	3-4 days
M67 x 0.75	3.0	0.10	#21-466	€170,00 Qty 10+ €161,50	3-4 days
M67 x 0.75	4.0	0.01	#21-467	€170,00 Qty 10+ €161,50	3-4 days
M52 x 0.75	0.3	50.00	#21-478	€74,00 Qty 10+ €70,30	3-4 days
M52 x 0.75	0.6	25.00	#21-479	€74,00 Qty 10+ €70,30	3-4 days
M52 x 0.75	0.9	12.50	#21-480	€74,00 Qty 10+ €70,30	3-4 days
M52 x 0.75	1.2	6.25	#21-481	€74,00 Qty 10+ €70,30	3-4 days
M52 x 0.75	2.0	1.00	#21-482	€130,00 Qty 10+ €123,50	Contact Us
M52 x 0.75	3.0	0.10	#21-483	€130,00 Qty 10+ €123,50	3-4 days
M52 x 0.75	4.0	0.01	#21-484	€130,00 Qty 10+ €123,50	3-4 days

M55 x 0.75	0.3	50.00	#21-495	€74,00 Qty 10+ €70,30	3-4 days
M55 x 0.75	0.6	25.00	#21-496	€74,00 Qty 10+ €70,30	3-4 days
M55 x 0.75	0.9	12.50	#21-497	€74,00 Qty 10+ €70,30	3-4 days
M55 x 0.75	1.2	6.25	#21-498	€74,00 Qty 10+ €70,30	3-4 days
M55 x 0.75	2.0	1.00	#21-499	€130,00 Qty 10+ €123,50	3-4 days
M55 x 0.75	3.0	0.10	#21-500	€130,00 Qty 10+ €123,50	In Stock
M55 x 0.75	4.0	0.01	#21-501	€130,00 Qty 10+ €123,50	3-4 days
M86 x 0.75	0.3	50.00	#21-512	€252,00 Qty 10+ €239,40	3-4 days
M86 x 0.75	0.6	25.00	#21-513	€252,00 Qty 10+ €239,40	3-4 days
M86 x 0.75	0.9	12.50	#21-514	€252,00 Qty 10+ €239,40	3-4 days
M86 x 0.75	1.2	6.25	#21-515	€252,00 Qty 10+ €239,40	3-4 days
M86 x 0.75	2.0	1.00	#21-516	€366,00 Qty 10+ €347,70	3-4 days
M86 x 0.75	3.0	0.10	#21-517	€366,00 Qty 10+ €347,70	3-4 days
M86 x 0.75	4.0	0.01	#21-518	€366,00 Qty 10+ €347,70	3-4 days
M22 x 0.75	0.3	50.00	#21-529	€87,00 Qty 10+ €82,65	3-4 days
M22 x 0.75	0.6	25.00	#21-530	€87,00 Qty 10+ €82,65	3-4 days
M22 x 0.75	0.9	12.50	#21-531	€87,00 Qty 10+ €82,65	3-4 days
M22 x 0.75	1.2	6.25	#21-532	€87,00 Qty 10+ €82,65	3-4 days
M22 x 0.75	2.0	1.00	#21-533	€142,00 Qty 10+ €134,90	3-4 days

M22 x 0.75	3.0	0.10	#21-534	€142,00 Qty 10+ €134,90	3-4 days
M22 x 0.75	4.0	0.01	#21-535	€142,00 Qty 10+ €134,90	3-4 days
M22.5 x 0.50	0.3	50.00	#21-546	€55,00 Qty 10+ €52,25	3-4 days
M22.5 x 0.50	0.6	25.00	#21-547	€55,00 Qty 10+ €52,25	3-4 days
M22.5 x 0.50	0.9	12.50	#21-548	€55,00 Qty 10+ €52,25	3-4 days
M22.5 x 0.50	1.2	6.25	#21-549	€55,00 Qty 10+ €52,25	3-4 days
M22.5 x 0.50	2.0	1.00	#21-550	€104,00 Qty 10+ €98,80	3-4 days
M22.5 x 0.50	3.0	0.10	#21-551	€104,00 Qty 10+ €98,80	3-4 days
M22.5 x 0.50	4.0	0.01	#21-552	€104,00 Qty 10+ €98,80	3-4 days
M37 x 0.50	0.3	50.00	#21-563	€68,00 Qty 10+ €64,60	3-4 days
M37 x 0.50	0.6	25.00	#21-564	€68,00 Qty 10+ €64,60	3-4 days
M37 x 0.50	0.9	12.50	#21-565	€68,00 Qty 10+ €64,60	3-4 days
M37 x 0.50	1.2	6.25	#21-566	€68,00 Qty 10+ €64,60	In Stock
M37 x 0.50	2.0	1.00	#21-567	€130,00 Qty 10+ €123,50	3-4 days
M37 x 0.50	3.0	0.10	#21-568	€130,00 Qty 10+ €123,50	3-4 days
M37 x 0.50	4.0	0.01	#21-569	€130,00 Qty 10+ €123,50	3-4 days
M35.5 x 0.50	0.3	50.00	#21-580	€68,00 Qty 10+ €64,60	3-4 days
M35.5 x 0.50	0.6	25.00	#21-581	€68,00 Qty 10+ €64,60	3-4 days
M35.5 x 0.50	0.9	12.50	#21-582	€68,00 Qty 10+ €64,60	3-4 days

M35.5 x 0.50	1.2	6.25	#21-583	€68,00 Qty 10+ €64,60	In Stock
M35.5 x 0.50	2.0	1.00	#21-584	€130,00 Qty 10+ €123,50	3-4 days
M35.5 x 0.50	3.0	0.10	#21-585	€130,00 Qty 10+ €123,50	3-4 days
M35.5 x 0.50	4.0	0.01	#21-586	€130,00 Qty 10+ €123,50	3-4 days
M72 x 0.75	0.3	50.00	#21-597	€136,00 Qty 10+ €129,20	3-4 days
M72 x 0.75	0.6	25.00	#21-598	€136,00 Qty 10+ €129,20	3-4 days
M72 x 0.75	0.9	12.50	#21-599	€136,00 Qty 10+ €129,20	3-4 days
M72 x 0.75	1.2	6.25	#21-600	€136,00 Qty 10+ €129,20	3-4 days
M72 x 0.75	2.0	1.00	#21-601	€204,00 Qty 10+ €193,80	3-4 days
M72 x 0.75	3.0	0.10	#21-602	€204,00 Qty 10+ €193,80	3-4 days
M72 x 0.75	4.0	0.01	#21-603	€204,00 Qty 10+ €193,80	3-4 days
M105 x 1.00	0.3	50.00	#21-614	€395,00 Qty 10+ €375,25	3-4 days
M105 x 1.00	0.6	25.00	#21-615	€395,00 Qty 10+ €375,25	3-4 days
M105 x 1.00	0.9	12.50	#21-616	€395,00 Qty 10+ €375,25	3-4 days
M105 x 1.00	1.2	6.25	#21-617	€395,00 Qty 10+ €375,25	3-4 days
M105 x 1.00	2.0	1.00	#21-618	€561,00 Qty 10+ €532,95	3-4 days
M105 x 1.00	3.0	0.10	#21-619	€561,00 Qty 10+ €532,95	3-4 days
M105 x 1.00	4.0	0.01	#21-620	€561,00 Qty 10+ €532,95	3-4 days

M62 x 0.75	0.3	50.00	#21-631	€94,00 Qty 10+ €89,30	3-4 days
M62 x 0.75	0.6	25.00	#21-632	€94,00 Qty 10+ €89,30	3-4 days
M62 x 0.75	0.9	12.50	#21-633	€94,00 Qty 10+ €89,30	3-4 days
M62 x 0.75	1.2	6.25	#21-634	€94,00 Qty 10+ €89,30	3-4 days
M62 x 0.75	2.0	1.00	#21-635	€145,00 Qty 10+ €137,75	3-4 days
M62 x 0.75	3.0	0.10	#21-636	€145,00 Qty 10+ €137,75	3-4 days
M62 x 0.75	4.0	0.01	#21-637	€145,00 Qty 10+ €137,75	3-4 days
M46 x 0.75	0.3	50.00	#21-648	€74,00 Qty 10+ €70,30	3-4 days
M46 x 0.75	0.6	25.00	#21-649	€74,00 Qty 10+ €70,30	3-4 days
M46 x 0.75	0.9	12.50	#21-650	€74,00 Qty 10+ €70,30	3-4 days
M46 x 0.75	1.2	6.25	#21-651	€74,00 Qty 10+ €70,30	Contact Us
M46 x 0.75	2.0	1.00	#21-652	€130,00 Qty 10+ €123,50	Contact Us
M46 x 0.75	3.0	0.10	#21-653	€130,00 Qty 10+ €123,50	Contact Us
M46 x 0.75	4.0	0.01	#21-654	€130,00 Qty 10+ €123,50	3-4 days
M40.5 x 0.50	0.3	50.00	#21-665	€74,00 Qty 10+ €70,30	3-4 days
M40.5 x 0.50	0.6	25.00	#21-666	€74,00 Qty 10+ €70,30	3-4 days
M40.5 x 0.50	0.9	12.50	#21-667	€74,00 Qty 10+ €70,30	3-4 days
M40.5 x 0.50	1.2	6.25	#21-668	€74,00 Qty 10+ €70,30	3-4 days
M40.5 x 0.50	2.0	1.00	#21-669	€130,00 Qty 10+ €123,50	3-4 days

M40.5 x 0.50	3.0	0.10	#21-670	€130,00 Qty 10+ €123,50	3-4 days
M40.5 x 0.50	4.0	0.01	#21-671	€130,00 Qty 10+ €123,50	3-4 days
M37.5 x 0.50	0.3	50.00	#21-682	€68,00 Qty 10+ €64,60	3-4 days
M37.5 x 0.50	0.6	25.00	#21-683	€68,00 Qty 10+ €64,60	3-4 days
M37.5 x 0.50	0.9	12.50	#21-684	€68,00 Qty 10+ €64,60	3-4 days
M37.5 x 0.50	1.2	6.25	#21-685	€68,00 Qty 10+ €64,60	3-4 days
M37.5 x 0.50	2.0	1.00	#21-686	€130,00 Qty 10+ €123,50	3-4 days
M37.5 x 0.50	3.0	0.10	#21-687	€130,00 Qty 10+ €123,50	3-4 days
M37.5 x 0.50	4.0	0.01	#21-688	€130,00 Qty 10+ €123,50	In Stock
M43 x 0.75	0.3	50.00	#21-699	€74,00 Qty 10+ €70,30	Contact Us
M43 x 0.75	0.6	25.00	#21-700	€74,00 Qty 10+ €70,30	3-4 days
M43 x 0.75	0.9	12.50	#21-701	€74,00 Qty 10+ €70,30	Contact Us
M43 x 0.75	1.2	6.25	#21-702	€74,00 Qty 10+ €70,30	Contact Us
M43 x 0.75	2.0	1.00	#21-703	€130,00 Qty 10+ €123,50	3-4 days
M43 x 0.75	3.0	0.10	#21-704	€130,00 Qty 10+ €123,50	3-4 days
M43 x 0.75	4.0	0.01	#21-705	€130,00 Qty 10+ €123,50	3-4 days
M34 x 0.50	0.3	50.00	#21-716	€68,00 Qty 10+ €64,60	Contact Us
M34 x 0.50	0.6	25.00	#21-717	€68,00 Qty 10+ €64,60	Contact Us

M34 x 0.50	0.9	12.50	#21-718	€68,00 Qty 10+ €64,60	3-4 days
M34 x 0.50	1.2	6.25	#21-719	€68,00 Qty 10+ €64,60	3-4 days
M34 x 0.50	2.0	1.00	#21-720	€130,00 Qty 10+ €123,50	3-4 days
M34 x 0.50	3.0	0.10	#21-721	€130,00 Qty 10+ €123,50	3-4 days
M34 x 0.50	4.0	0.01	#21-722	€130,00 Qty 10+ €123,50	3-4 days
M58 x 0.75	0.3	50.00	#21-733	€74,00 Qty 10+ €70,30	3-4 days
M58 x 0.75	0.6	25.00	#21-734	€74,00 Qty 10+ €70,30	3-4 days
M58 x 0.75	0.9	12.50	#21-735	€74,00 Qty 10+ €70,30	3-4 days
M58 x 0.75	1.2	6.25	#21-736	€74,00 Qty 10+ €70,30	3-4 days
M58 x 0.75	2.0	1.00	#21-737	€135,00 Qty 10+ €128,25	3-4 days
M58 x 0.75	3.0	0.10	#21-738	€135,00 Qty 10+ €128,25	3-4 days
M58 x 0.75	4.0	0.01	#21-739	€135,00 Qty 10+ €128,25	3-4 days
M25.5 x 0.50	0.3	50.00	#21-750	€55,00 Qty 10+ €52,25	3-4 days
M25.5 x 0.50	0.6	25.00	#21-751	€55,00 Qty 10+ €52,25	3-4 days
M25.5 x 0.50	0.9	12.50	#21-752	€55,00 Qty 10+ €52,25	3-4 days
M25.5 x 0.50	1.2	6.25	#21-753	€55,00 Qty 10+ €52,25	3-4 days
M25.5 x 0.50	2.0	1.00	#21-754	€104,00 Qty 10+ €98,80	3-4 days
M25.5 x 0.50	3.0	0.10	#21-755	€104,00 Qty 10+ €98,80	Contact Us
M25.5 x 0.50	4.0	0.01	#21-756	€104,00 Qty 10+ €98,80	3-4 days

M30.5 x 0.50	0.3	50.00	#21-767	€68,00 Qty 10+ €64,60	3-4 days
M30.5 x 0.50	0.6	25.00	#21-768	€68,00 Qty 10+ €64,60	3-4 days
M30.5 x 0.50	1.2	6.25	#21-770	€68,00 Qty 10+ €64,60	3-4 days
M30.5 x 0.50	2.0	1.00	#21-771	€116,00 Qty 10+ €110,20	3-4 days
M30.5 x 0.50	3.0	0.10	#21-772	€116,00 Qty 10+ €110,20	3-4 days
M30.5 x 0.50	4.0	0.01	#21-773	€116,00 Qty 10+ €110,20	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com